




# QTH41

DVR Technology	BNC HD
Channels	4
Recording Resolution	1080L, 720p, 960H,
Live Viewing Resolution	1080p / 720p / 960H
Live Display FPS	30 FPS per Channel
Hard Drive	Supports 1 HDD up to 6TB
Remote Monitoring	10 Simultaneous Users
Compatibility	Mac and PC
Connects With	Local Cameras
Monitor Connections	HDMI, VGA



Supports QTH BNC HD Cameras & Analog Cameras

## DVR

Video Compression	H.264
Live Display Resolution	1080p, 720p, 800x600
Live Display FPS	30 FPS
Display Modes	1, 4, Auto Sequence
Languages	English, Chinese (Simplified & Traditional), Czech, French, Portuguese, Spanish, Turkish, Bulgarian, Greek, Italian, German, Russian, Polish, Japanese, Indonesian, Thai, Hungarian, Lithuanian, Vietnamese, Dutch, Swedish, Norwegian, Persian, Arabic, Romanian

## RECORDING RESOLUTION OPTIONS

1080L	928 x 960 pixels
720P Resolution	1280 x 720 pixels
960H Resolution	960 x 480 pixels

## RECORDING MODES

Recording Modes	Manual, Time Schedule, Motion Detection
Backup Methods	PC, Flash, USB Hard Drive

## PLAYBACK ON DVR

Playback Speed	1080L at 30FPS per channel	120 FPS total
	720P at 30 FPS per channel	120 FPS total
	960H at 30 FPS per channel	120 FPS total
Number Channels	4 Simultaneous Local Playback	

## REMOTE MONITORING

Scan 'N View	Yes
Dual Stream	CIF
Simultaneous Users	10

## COMPATIBILITY

Software Support	QT View
Mobile Support	iPhone, iPad, Android
Computer Support	WinXP, Vista, Win7/8, Mac OS 10.7/10.8/10.9/10.10

## VIDEO, AUDIO & ALARM PORTS

Video in	4 BNC
Video Out	HDMI, VGA,
Alarm In	None
Alarm Out	None
Audio In	1 RCA
Audio Out	1 RCA

## COMMUNICATION PORTS

Network	RJ45 10/100 Mbps
USB	2 USB 2.0
eSATA	None

## ACCESSORIES

Control	USB Mouse, Remote Control
Connectors / Cables	HDMI Cable,
Mounting Hardware	Screws for Hard Drives
Other	Quick Start Guide

## (QTH41 cont'd...)

### HARD DRIVES

Maximum Size	6TB
Number Supported	1

### PTZ

PTZ Support	Through BNC Video In ports
Supported Protocols	Null, Pelco D, Pelco D, Lilin, Minking, Neon, Star, VIDO, DSCP, VISCA, Samsung, RM110, HY

### POWER

Power Supply	12v 2a
Power Consumption	<6w (w/o HD)

### PHYSICAL

Weight	1.8 lbs
Dimensions	10" W X 8.25" D X 1.75" H
Operating Temperature	14° – 130° F

