

QTH8

DVR Technology	BNC HD
Channels	8
Recording Resolution	720p, 960H, D1
Live Viewing Resolution	1080p / 720p / 960H / 704 x 480
Live Display FPS	30 FPS per Channel
Hard Drive	Supports 1 HDD up to 4TB
Remote Monitoring	10 Simultaneous Users
Compatibility	Mac and PC
Connects With	Local Cameras
Monitor Connections	HDMI, VGA



Supports QTH BNC HD Cameras & Analog Cameras

DVR

Video Compression	H.264
Live Display Resolution	1080p, 720p, 1280x1024, 1024x768, 960H, 704x480
Live Display FPS	30 FPS
Display Modes	1, 4, 8, Auto Sequence
Languages	English, Chinese (Simplified & Traditional), Czech, French, Portuguese, Spanish, Turkish, Bulgarian, Greek, Italian, German, Russian, Polish, Japanese, Indonesian, Thai, Hungarian, Lithuanian, Vietnamese, Dutch, Swedish, Norwegian, Persian, Arabic, Romanian

RECORDING RESOLUTION OPTIONS

720P Resolution	1280 x 720 pixels
960H Resolution	960 x 480 pixels
D1 Resolution	704 x 480

RECORDING MODES

Recording Modes	Manual, Time Schedule, Motion Detection
Backup Methods	PC, Flash, USB Hard Drive

PLAYBACK ON DVR

Playback Speed	720P at 30 FPS per channel	240 FPS total
	960H at 30 FPS per channel	240 FPS total
	D1 at 30 FPS per channel	240 FPS total
Number Channels	8 Simultaneous Local Playback	

REMOTE MONITORING

Scan 'N View	Yes
Dual Stream	CIF
Simultaneous Users	10

COMPATIBILITY

Browser Support	IE, Firefox & Chrome (with IE plugin), Safari
Mobile Support	iPhone, iPad, Android
Computer Support	WinXP, Vista, Win7/8, Mac OS 10.7/10.8/10.9/10.10

VIDEO, AUDIO & ALARM PORTS

Video in	8 BNC
Video Out	HDMI, VGA,
Alarm In	None
Alarm Out	None
Audio In	1 RCA
Audio Out	1 RCA

COMMUNICATION PORTS

Network	RJ45 10/100 Mbps
USB	2 USB 2.0
eSATA	None

ACCESSORIES

Control	USB Mouse, Remote Control
Connectors / Cables	HDMI Cable,
Mounting Hardware	Screws for Hard Drives
Other	Quick Start Guide

(QTH8 cont'd...)

HARD DRIVES

Maximum Size	4TB
Number Supported	1

PTZ

PTZ Support	None
Supported Protocols	None

POWER

Power Supply	12v 2a
Power Consumption	<8w (w/o HD)

PHYSICAL

Weight	1.2 lbs
Dimensions	8"W X 8.25"D X 2"H
Operating Temperature	32°– 122°F

