

## WM14T390GB

### Automatic washing machine




**A+++**

iSensoric Washing Machine with iQDrive for highly effective and efficient laundry care with large easy-to read display.

- ✓ Intelligent and powerful iQdrive motor with 10-year warranty for highly effective and efficient laundry care.
- ✓ With the option speedPerfect, get perfect washing results in up to 65% less time.
- ✓ Sensor-controlled wash programmes for the most efficient water usage with any load size - thanks to waterPerfect Plus.
- ✓ A+++ -30 %: washes 30 % more efficient than the requirement for energy efficiency class A+++.

#### Features

##### Technical Data



Built-in / Free-standing : Free-standing  
 Door hinge : Left  
 Color / Material body : White  
 Length electrical supply cord (cm) : 210  
 Height for building under : 850.00  
 Height of the product (mm) : 848  
 Dimensions of the product (mm) : 848 x 598 x 550  
 Wheels : No  
 Net weight (kg) : 70.0  
 Drum volume (l) : 58  
 Main colour of product : White  
 Door Frame : silver-white  
 Noise level washing (dB(A) re 1 pW) : 51  
 Connection Rating (W) : 2300  
 Current (A) : 10  
 Voltage (V) : 220-240  
 Frequency (Hz) : 50  
 Cord Included : No  
 Plug type : GB plug  
 Length of drain hose (in) : 59.05  
 Length of supply hose (in) : 59.05  
 Appliance Dimensions (h x w x d) (inches) : x x  
 Dimensions of the packed product (in) : 33.85 x 24.80 x 26.77  
 Net weight (lbs) : 153  
 Gross weight (lbs) : 155  
 Length of drain hose : 150.00  
 Length of supply hose : 150.00  
 Gross weight (kg) : 71.0  
 Connection Rating (W) : 2300  
 Current (A) : 10  
 Voltage (V) : 220-240  
 Frequency (Hz) : 50  
 Approval certificates : CE  
 Water protection system : Multiple water protection  
 Number of Options : 5  
 Spin speed options : Variable  
 Internal water heater included : No  
 Digital countdown indicator : Yes  
 Drying progress indicator : LED-display



4 242003 765142

#### Optional accessories

WMZ2380 Extension for cold water inlet /Aquastop  
 WMZ2200 Floor securing component  
 WMZ20490 Platform with pull-out  
 WMZ20430 Built-under kit

## WM14T390GB

### Automatic washing machine

Features	
<ul style="list-style-type: none"><li>• iQdrive, Extraklasse</li></ul> <p><b>engine power and consumption</b></p> <ul style="list-style-type: none"><li>• rated capacity: 8 kg</li><li>• Energy Efficiency Class: A+++ -30%</li><li>• 30% more economical (135 kWh/year) than the standard value (196 kWh/year) of energy efficiency class A+++ in category 8 kg according to the EU-order 1061/2010</li><li>• Energy consumption 135 kWh per year, based on 220 standard washing cycles for cotton programmes at 60°C and 40°C at full and partial load, and the consumption of the low power modes. Actual energy consumption will depend on how the appliance is used.</li><li>• energy consumption of the standard 60 °C cotton programme 0.77 kWh at full load and 0.54 kWh at partial load and of the standard 40 °C cotton programme 0.4 kWh at partial load</li><li>• weighted power consumption off-mode / left-on mode: 0.12 W / 0.58 W</li><li>• Water consumption 9680 litres per year, based on 220 standard washing cycles for cotton programmes at 60°C and 40°C at full and partial load. Actual water consumption will depend on how the appliance is used.</li><li>• spin-drying efficiency class: B</li><li>• max. spin speed: 1400 rpm max. remaining moisture: 53 %</li><li>• Indication that cotton 60° Eco and cotton Eco 40° are the standard washing programmes to which the information in the label and the fiche relates, that these programmes are suitable to clean normally soiled cotton laundry and that they are the most efficient programmes in terms of combined energy and water consumption. The actual temperature may vary with this combination from the specified program temperature. Washing times will be extended for the benefit of lower energy consumption. Washing effect A is always guaranteed in the process.</li><li>• programme time of the standard 60 °C cotton programme 224 min at full load and 224 min at partial load and of the standard 40 °C cotton programme 224 min at partial load</li><li>• Duration of the left-on mode: 15 min</li><li>• Noise level washing in standard 60° cotton programme at full load in dB (A) re 1 pW: 51</li><li>• Noise level spinning at standard 60°C cotton programme at full loading in dB (A) re 1 pW: 77</li></ul> <p><b>programmes</b></p> <ul style="list-style-type: none"><li>• Special programmes: Jeans, quick/mixture, hygiene, Quick 15'/30', wool, delicates/silk</li></ul> <p><b>options</b></p> <ul style="list-style-type: none"><li>• varioPerfect: time- or energy optimized programs with perfect performance</li><li>• touchControl buttons: Start delay, start/pause with reload function, ecoPerfect/speedPerfect, Water &amp; Rinse Plus, Spin speed reduction/ Rinse hold</li></ul>	<p><b>comfort and safety</b></p> <ul style="list-style-type: none"><li>• Drum volume: 58 l</li><li>• waveDrum: for highly effective and extremely gentle laundry care</li><li>• 32 cm porthole, silver-white with 165° opening door</li><li>• Metal door closing hook</li><li>• comfort lock</li><li>• iQdrive: most energy-saving and quietest motortechnologie</li><li>• 10 years guaranty on iQdrive</li><li>• anti-vibration Design: more stability and quietness</li><li>• Flow sensor for optimal wateruse</li><li>• waterPerfect Plus: resource gentle watermanagement</li><li>• Multiple water protection</li><li>• Aquatronic wash system</li><li>• Continuous automatic load adjustment system</li><li>• Fully electronic control dial for wash programmes, temperature and special programmes</li><li>• Large LED-Display for programme status indication, max. spin speed, remaining time, 24 h end time delay and load recommendation</li><li>• Overdosage indication</li><li>• Foam detection system</li><li>• Unbalanced load detection</li><li>• Childproof</li><li>• buzzer at end of program</li><li>• Self cleaning detergent drawer</li><li>• Divider for Liquid Detergent</li></ul> <p><b>technical information</b></p> <ul style="list-style-type: none"><li>• slide-under at height of 85 cm</li><li>• Dimensions (H x W x D): 84.8 cm x 59.8 cm x 55.0 cm</li></ul>