

ICIP-B1300-VIR

1.3 Megapixel Indoor/Outdoor, Full-Size IP Bullet IR Camera



A weatherproof, day/night 1.3 Megapixel bullet camera – the ICIPB1300VIR. This sleek bullet design contains a high resolution 1.3 Megapixel Progressive Scan Aptina CMOS sensor, capable of outputting a crisp, clear image. The optics are located behind the removable black snout, which conceals the 2.8-12mm vari-focal lens. This camera is IP 66 rated and highly weatherproof. This camera is fully accessible via the entire ICR software suite, and is also compatible with third party ONVIF recorders and streamers. This camera also comes equipped with an audio input for external microphones, alarm I/O's, and support for PoE power.

Features

- 2.8-12mm Varifocal Lens
- IP66, PoE
- Micro SD memory
- Max. IR LEDs length 60 FT
- Built-in 2/1 alarm in/out

ICIP-B1300-VIR

Specifications

Model	ICIP-B1300-VIR
Camera	
Image Sensor	1/3" 1.3Megapixel Aptina CMOS
Effective Pixels	1280(H)×960(V)
Scanning system	Progressive
Electronic Shutter Speed	Auto/Manual, 1/4~1/10000s
Min. Illumination	0.1Lux/F1.2 (Color), 0.005Lux/F1.2(B/W);0Lux/F1.2(IR on)
S/N Ratio	>50dB
Video Output	1 channel, BNC(1.0Vp-p/75Ω)
Camera Features	
Max IR LEDs Length	60ft (20m)
Day/Night	Auto (ICR) / Color / B/W
Backlight Compensation	BLC / HLC / DWDR
White Balance	Auto
Gain Control	Auto / Manual
Noise Reduction	2D
Privacy Masking	Up to 4 areas
Lens	
Focal Length	2.8 ~ 12mm
Max Aperture	F1.4
Focus Control	Manual
Angle of View	H: 92°(Wide) ~ 27.2°(Tele)
Lens Type	Manual / Auto Iris (DC)
Mount Type	Board-in Type
Video	
Compression	H.264 / MJPEG
Resolution	1.3M(1280x960) / 720P(1280x720) / D1(704x480) / CIF(352x240)
Frame Rate	Main Stream: 1.3M/720P(1 ~ 25/30fps) Sub Stream: D1/CIF(1 ~ 25/30fps)
Bit Rate	H.264: 32K ~ 8192Kbps, MJPEG: 32K ~ 12288Kbps
Audio	
Compression	G.711a / G.711u(64kbps) / PCM(128kbps)
Interface	1/1 channel In/Out
Network	
Ethernet	RJ-45 (10/100Base-T)
Protocol	IPv4/IPv6, HTTP, HTTPS, SSL, TCP/IP, UDP, UPnP, ICMP, IGMP, SNMP, RTSP, RTP, SMTP, NTP, DHCP, DNS, PPPOE, DDNS, FTP, IP Filter, QoS, Bonjour
ONVIF	ONVIF Ver. 2.0
Max. User Access	10 users
Smart Phone	iPhone, iPad, Android, Windows Phone
Auxiliary Interface	
Memory Slot	Micro SD, Max 32GB
Alarm	2/1 channel In/Out

General	
Power Supply	DC12V, PoE (802.3af)
Power Consumption	<10W
Working Environment	-40°F ~ 140°F / -40°C ~ 60°C, 10%~90%
Ingress Protection	IP66
Dimensions	φ4.09" × 12.07" / φ104mm × 306.7mm
Weight	2.75lb / 1.25Kg

Optional Accessories



MNT-JUNCTION BOX 4



MNT-PCNRIP



MNT-POLIP

IC Realtime LLC

3050 N Andrews Avenue Extension
Pompano Beach, FL 33064
(866) 997-9009

www.icrealtime.com

Designs and specifications subject to change without notice. Copyright © 2015 IC Realtime, LLC. All rights reserved.