

ICIP-D1300VIR

1.3 MP Indoor/Outdoor, Vandalproof IR IP Dome Camera



1.3 Megapixel Dome Style Camera works seamlessly with IC Realtime NVRs, Hybrid DVRs and Management Software.

Features

- 2.8~12mm varifocal lens
- H.264 & MJPEG dual-stream encoding
- Max 25/30fps@1.3M(1280×960)&25/30fps@720P(1280×720)
- Multiple network monitoring: Web browser, Smart ICRSS, ICRSS Pro/ICVIEW
- D-WDR, Day/Night(ICR), 2DNR, Auto iris, AWB, AGC, BLC
- 1.3Megapixel D-WDR HD Vandal-proof IR Network Dome Camera
- **UL Listed 60950**

ICIP-D1300VIR

Specifications

Model	ICIP-D1300VIR
Camera	
Image Sensor	1/3" 1.3Megapixel Aptina CMOS
Effective Pixels	1280(H)×960(V)
Scanning system	Progressive
Electronic Shutter Speed	Auto/Manual 1/4~1/10000
Min. Illumination	Color: 0. 1LUX/F1.4, B/W: 0.005LUX/F1.4,0Lux (IR on)
S/N Ratio	>50dB
Video Output	1 channel, Push Terminal (1.0Vp-p/75Ω)
Camera Features	
Max IR LEDs Length	60FT
Day/Night	Auto(ICR) / Color / B/W
Backlight Compensation	BLC
White Balance	Auto
Gain Control	Auto / Manual
Noise Reduction	2D
Privacy Masking	Up to 4 areas
Lens	
Focal Length	2.8~12mm
Max Aperture	F1.4
Focus Control	Manual
Angle of View	H: 92°(Wide)~27.2°(Tele)
Lens Type	Manual/Auto Iris (DC)
Mount Type	Board-in Type
Video	
Compression	H.264 / MJPEG
Resolution	1.3M(1280×960) / 720P(1280×720) / D1(704×480) / CIF(352×240)
Frame Rate	Main Stream: 1.3M/720P(1 ~ 25/30fps) Sub Stream: D1/CIF(1 ~ 25/30fps)
Bit Rate	H.264: 32K ~ 8192Kbps, MJPEG: 32K ~ 12288Kbps
Audio	
Compression	G.711a / G.711u (64kbps)/ PCM(128kbps)
Interface	1/1 channel In/Out
Network	
Ethernet	RJ-45 (10/100Base-T)
Protocol	IPv4/IPv6, HTTP, HTTPS, SSL, TCP/IP, UDP, UPnP, ICMP, IGMP, SNMP, RTSP, RTP, SMTP, NTP, DHCP, DNS, PPPOE, DDNS, FTP, IP Filter, QoS, Bonjour
ONVIF	ONVIF Ver. 2.0
Max. User Access	10 users
Smart Phone	iPhone, iPad, Android, Windows Phone
Auxiliary Interface	
Memory Slot	Micro SD, Max 32GB
Alarm	1/1 channel In/Out

General	
Power Supply	DC12V, PoE (802.3af)
Power Consumption	< 8W
Working Environment	-14°F ~ 140°F / -25°C ~ 60°C, 10%~90%
Protection Level	IK10 & IP66
Dimensions	Φ5.94"×4.68mm ~ Φ151×119mm
Weight	2.31lb ~ 1.05kg

ICIP-D1300VIR

Optional Accessories



[MNT-ARM-MPB300S](#)



[MNT-BOX-MPA120](#)



[MNT-DVIR-MPA100](#)



[MNT-PCNRIP](#)



[MNT-POLIP](#)