

Cat6 Gigabit Snagless Slim UTP Ethernet Cable (RJ45 M/M), Blue, 4 ft. (1.22 m)

MODEL NUMBER: **N201-S04-BL**



Highlights

- Over 38% slimmer than standard Cat6 cables
- Rated for Cat6 Gigabit/1 Gbps communications
- Snagless RJ45 male connectors
- Easy to route through cable management panels
- High-quality 28 AWG copper wire

Package Includes

- N201-S04-BL Cat6 Gigabit Snagless Slim UTP Patch Cable (RJ45 M/M), 4 ft.

Connects network components like printers, computers, copiers, routers, servers, modems and switches.

Ideal for high-density data centers. Slim design increases airflow in tight spaces.

Features

Perfect Solution for Your Networking Needs

- Ideal for connecting components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- Delivers speeds up to Cat6 Gigabit/1 Gbps

Special Slim Design

- More than 38% smaller in diameter than standard Cat6 cable
- Increases airflow in tight spaces
- Extra flexible for installing around corners and through cable management panels

Premium Construction for Superior Performance

- Made from 28 AWG copper wire
- PVC 4-pair stranded UTP
- RJ45 male connectors
- Integral strain relief for long life

Snagless Connectors

- snagless boots prevent locking tabs from damage

Specifications

OVERVIEW	
UPC Code	037332193063
Technology	Cat6
PHYSICAL	
Color	Blue
Cable Shielding	UTP
Wire Type	Stranded
Wire Gauge (AWG)	28
Cable Length (ft.)	4
Cable Length (m)	1.2
Cable Length (in.)	48
Cable Length (cm)	121.9
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.07
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
Cable Style	Slim; Snagless; Molded; Unshielded
SPECIAL FEATURES	
Snagless Connector	Yes
STANDARDS & COMPLIANCE	
Certifications	RoHS
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>