

## Duplex Singlemode 9/125 Fiber Patch Cable (LC/ST), 25 m (82 ft.)

MODEL NUMBER: **N368-25M**



Premium singlemode fiber optic cabling transmits fast, clear data signals through your LAN with twice the bandwidth throughput of multimode cable.

### Features

#### Fast, Clear Data Transmission Through Your LAN

- Twice the bandwidth throughput of multimode cable
- Ideal for network equipment that requires singlemode fiber optic patch cables
- Attenuation loss meets or exceeds latest industry standards

#### Superior Construction for Error-Free Signal Transfer

- 9/125 duplex (zipcord) fiber made from glass
- Sturdy LC and ST male connectors meet stringent insertion loss standards
- Beveled edge on glass ends for easy plug insertion
- Yellow-colored for identification as singlemode

## Specifications

OVERVIEW	
UPC Code	037332138262
Technology	Singlemode
Optical Mode	OS2
PHYSICAL	
Color	Yellow

### Highlights

- Attenuation loss meets or exceeds latest industry standards
- 9/125 duplex (zipcord) fiber made from glass
- LC and ST male connectors meet insertion loss standards
- Low Smoke Zero Halogen (LSZH) jacket
- Beveled edge on glass ends for easy plug insertion

### System Requirements

- Fiber optic hardware or NIC card requiring singlemode duplex cable with LC/ST connectors

### Package Includes

- N368-25M Duplex Singlemode 9/125 Fiber Patch Cable, 25 m



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Clad Diameter	125 micron
Core Diameter	9 micron
Number of Fibers	2
Cable Length (ft.)	82
Cable Length (m)	25
Cable Length (in.)	984.3
Shipping Dimensions (hwd / cm)	26.67 x 30.48 x 1.27
Shipping Dimensions (hwd / in.)	10.50 x 12.00 x 0.50
Shipping Weight (kg)	0.20
Shipping Weight (lbs.)	0.44
<b>CONNECTIONS</b>	
Side A - Connector 1	LC DUPLEX (MALE)
Side A - Connector 2	SC DUPLEX (MALE)
Side B - Connector 1	ST DUPLEX (MALE)
<b>SPECIAL FEATURES</b>	
Push/Pull Tabs	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>