



# IKS-WB9518

## 4K Ultra HD Resolution IP Box Camera

### Ultra High Definition 4K

The IKS-WB9518 is a 4K IP box camera with Ultra HD resolution (3840 x 2160) that delivers four times the imaging power of standard HD (1920 x 1080). Ultra HD is ideal for large area coverage or fast moving, high traffic locations, where it can precisely identify objects even when zooming in at great distances. A C/CS lens mount allows for a wide variety of lens options, while Digital WDR and True D/N make it flexible for almost any application.

- 4K Ultra HD resolution
- C/CS lens mount (lens not included)
- ONVIF compatibility
- Power over Ethernet (802.3af)
- MicroSD card for edge recording
- Digital WDR and True D/N captures images in difficult lighting



### Camera

<b>Image sensor</b>	1/1.9 inch CMOS 4K
<b>Effective pixels</b>	3840 x 2160
<b>Lens</b>	-
<b>Lens type</b>	C/CS (lens not included)
<b>Angle of view</b>	-
<b>Zoom</b>	-
<b>Min. illumination</b>	0.05 lux @F1.8 (color) 0.005 lux @F1.8 (B/W)
<b>IR illuminators</b>	-

### Camera Features

<b>Day/Night</b>	Yes, IR cut filter
<b>Wide Dynamic Range</b>	Digital WDR
<b>White balance</b>	Auto, manual, ATW One push (2700- 7800K)
<b>Gain (AGC)</b>	Auto
<b>BLC</b>	Yes
<b>Privacy mask</b>	Yes
<b>Motion detection</b>	Yes
<b>Tamper protection</b>	Yes

### Video

<b>Compression</b>	H.264, MJPEG
<b>Resolutions</b>	3840x2160, 3200x1800, 1920x1080, 1280x1024, 1280x720, 1024x768, 800x600, 720x480, 640x480, 352x240, 320x240
<b>Video streams</b>	4 streams
<b>Frame rate (max)</b> <sup>1</sup>	25 fps@4K, 30fps@2K

### Interface

<b>Digital in/out</b>	1 IN/1 OUT
<b>Ethernet connections</b>	10Base-T/100Base-TX, RJ45
<b>SD card slot</b>	MicroSDXC 64GB max

### Audio

<b>Audio compression</b>	G.726, G711
<b>Audio in/out</b> <sup>2</sup>	MIC In, Line OUT (1 Vrms)

<sup>1</sup>: Varies in accordance with the object, image quality, network environment and performance of the personal computer used.

<sup>2</sup>: The sound may not be clear depending on the conditions of the lines.

### PART NUMBERS

Part Number	Description
9518-KIT36-10	IKS-WB9518 w/3.6-10mm lens
IKS-WB9518	IKS-WB9518 camera only

### Network

<b>Protocols</b>	IPv4, IPv6, TCP/IP, HTTP, HTTPS, UPnP, RTSP/RTP/ RTCP, IGMP, SMTP, FTP, DHCP, NTP, DNS, DDNS, PPPoE, QoS, SNMP, and 802.1X
<b>ONVIF</b>	Profile-S
<b>Maximum user access</b>	20 accounts
<b>Security</b>	User password
<b>Basic authorization</b>	Basic, Digest
<b>Bandwidth control</b>	QoS
<b>Camera set-up program</b>	Device search
<b>Plug-In</b>	Active X
<b>Alarm recording</b>	FTP, email, MicroSD card

### General

<b>Dimensions</b>	5.9" (L) x 3.1" (W) x 2" (H) (148mm x 79mm x 52mm)
<b>Weight</b>	0.87 lbs (395g)
<b>Power requirements</b>	802.3af PoE class 3, 12V DC ±10%
<b>Power consumption</b>	8.5W max
<b>Operation temperature</b>	14°F to 122°F (-10°C to 50°C)
<b>Operation humidity</b>	~ 90%
<b>Approvals</b>	FCC, UL, cUL, ITE
<b>Warranty</b>	2 years

### System Requirements

<b>Web browser support</b>	Internet Explorer® Ver. 8.0 or later
<b>Supported OS</b>	Windows XP, Windows Vista Business, Windows 7 Professional

### Accessories

<b>Included</b>	Power switch connector, back focus adjuster
-----------------	--

### 4K resolution vs. HD resolution

