


3MP Indoor/Outdoor Bullet IP Camera

O3VLB3 2.8mm fixed lens, dark grey housing

Features

- Supports 3MP @ 20fps and 1080p @ 30fps
- Built-in standard PoE (IEEE 802.3af)
- True Day/Night operation (IR cut filter)
- IR Range: 98' (depending on scene reflection)
- Supports H.264 and MJPEG codecs
- IP67 compliant
- 2 year warranty



Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 3.0MP
Maximum Resolution	2304x1296
Minimum Illumination	F2.0, Color: 0.37 lux, BW: 0 lux
White Balance	Auto, Manual
Exposure Control	Yes
Digital Slow Shutter	Yes
Backlight	BLC/HLC/D-WDR
Day/Night	IR cut filter
DNR	3D

Video Specifications

Main Resolution	2304x1296 @ 20fps, 1920x1080 / 1280x720 @ 30fps
Compression	H.264 (HP/MB/BP), MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	2 streams

External Terminal Specifications

Ethernet	10/100 Mbps
Power	DC jack

Network Specifications

Protocols	IPv4/IPv6, TCP, UDP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, DNS
DDNS support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP address filtering, digest authentication, user access log, HTTPS
User Access	20 users max. Number of simultaneous users may vary depending on resolution

System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection (4 regions), Tamper detection
Alarm Triggers	Analytics
Alarm Events	Email, record, snapshot
Video Buffer	Configurable pre-record & post-record
Image Settings	Privacy mask, corridor mode

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up, Chrome, Firefox)
---------------------	--

Operating & Unit Specifications

Power Supply	PoE, 12VDC (power supply not included)
Power Consumption	4W
Operating Temperature	-20° F – 140° F
Operating Humidity	Less than 95% RH
Unit Dimensions	6.49" (L) x 2.75" (Dia.)
Unit Weight	13 oz.
Certifications	FCC, RoHS
Included in Package	Unit, CD (manual, software), mounting screws, L wrench

Optional Accessories



POEINJ
12.95W
PoE Injector



PSW5
12VDC
Power Supply