BUSINESS COLOR LASER PRINTER

For Workgroups with Higher Print Volumes

HL-L9300CDWT

brother
at your side

HL-L9300CDWT

Ideal for mid-sized workgroups with higher print volumes, the Brother HL-L9300CDWT color laser printer delivers fast, low cost, high-impact business documents. Print more for less with the included super high-yield toner cartridges and low cost replacement cartridges. This high-performance printer offers flexible paper handling with dual paper trays, and for even greater capacity an optional tray expands total capacity to 1,300 sheets. Advanced security features provide network user authentication and help prevent against unauthorized access. Plus, easily share on your network with Ethernet or wireless interfaces and print from mobile devices□.

Specifications:

Print Technology	Color Laser
LCD Display (type/size)	1.8" Color Touchscreen
Paper Size	Upper/Lower Paper Trays: Up to 8.5" x 14" (legal) Multi-Purpose Tray: 3.0"-8.5" (W) / 5.0"-14" (L)
Print Speed (maximum)	Black : up to 32ppm Color: up to 32ppm
Time to First Page▼	Black: < 15 seconds Color: < 15 seconds
Print Resolution (maximum)	Up to 2400 x 600 dpi
Processor	400MHz
Emulations	PCL6, BR-Script3◇
Duplex Printing Capability	Yes
Paper Input Capacity (maximum)∞	(1) 250-Sheet Capacity Paper Tray, (1) 500-Sheet Capacity Paper Tray, and a 50-Sheet Capacity Multi-Purpose Tray
Optional Input Capacity (maximum)♦	1,300 sheets via optional tray
Output Capacity (maximum)∞	150 sheets (face down), 1 sheet (face up)
Media Types	Plain Paper, Thin/Thick Paper, Recycled Paper, Bond, Labels, Envelopes and Glossy Paper
Media Weights	Upper/Lower Paper Tray: 16-28 lbs. (bond) Multi-Purpose Tray: 16-43 lbs. (bond)
Memory (std. / max.)	128MB / 384MB♦
Standard Interfaces	Wireless 802.11b/g/n, Ethernet, Hi-Speed USB 2.0
USB Host	Yes, front
Operating Systems Compatibility	Windows®: XP Home / XP Professional / XP Professional x64 Edition / Windows Vista® / Windows® 7, 8, 8.1, 10 / Windows Server® 2003 (32 / 64 bit) / 2008 / 2008 R2 / 2012 / 2012 R2 Mac® OS X® v10.7.5, 10.8.x, 10.9.x, 10.10.x Linux
Mobile Device Compatibility□	AirPrint™, Google Cloud Print™, Brother iPrint&Scan (free downloadable app), Cortado Workplace, Mopria®, and Wi-Fi Direct®
Web Connect△	GOOGLE DRIVE™, ONEDRIVE®, DROPBOX, BOX
Security Features	Secure Function Lock, Active Directory® (using LDAP), Enterprise Security (802.1x), Secure Print, SSL/TLS, IPSec
Warranty	1-year Limited Warranty

Key Features at a Glance:

- Fast, business-critical printing at up to 32ppm black and color
- Low cost output due to super high-yield toner cartridges (6,000 pages^ black and color) – included for extra value
- Advanced Security features
  - Secure Function Lock lets you administer color printing controls and limitations on a per user or group basis (up to 100 users)
  - Active Directory® for network user authentication
- Dual paper trays (250-sheet and 500-sheet) adjustable for letter or legal and a 50-sheet capacity multi-purpose tray for envelopes or alternative media types (total capacity expandable to 1,300 sheets with optional add-on tray)
- Easily share with others via wireless or Ethernet networking
- Automatic duplex (two-sided) printing
- Mobile device printing□
- Adjustable color Touchscreen display for direct printing from popular business cloud services△
- One-year limited warranty with free phone support for the life of your product

Supplies & Accessories♦:

TN339BK	Super High-yield Black Toner Cartridge (6,000 pgs)^
TN339C	Super High-yield Cyan Toner Cartridge (6,000 pgs)^
TN339M	Super High-yield Magenta Toner Cartridge (6,000 pgs)^
TN339Y	Super High-yield Yellow Toner Cartridge (6,000 pgs)^
DR331CL	Drum Unit (25,000 pgs)**
BU320CL	Belt Unit (50,000 pgs A4/Letter)
WT320CL	Waste Toner Box (50,000 pgs)^^
LT-328CL	Optional 500-Sheet Capacity Paper Tray
BP60MPLTR	Multi-Purpose Paper (Letter, 500 sheets)

▼ From Ready mode and standard tray.
◇ PostScript®3™compatible.
∞ Maximum capacity based on using 20 lb. paper.
♦ Additional purchase required.
□ Requires connection to a wireless network. See www.connectprintshare.com for more details, availability and mobile device compatibility.
^ Approximate yield in accordance with ISO/IEC 19798 (Letter/A4).
** Drum yield is approximate and may vary based on type of use.
^^ Approximate yield based on A4 or Letter size single-sided pages.
△ Requires an Internet connection and an account with desired service. See www.connectprintshare.com for details.