

E2475SWJ



MODEL: E2475SWJ DATA SHEET

GENERAL FEATURES

panel type:	TN
screen size:	24"
viewable image size:	23.6"
aspect ratio:	16:9
brightness:	250 cd/m2
contrast ratio (DCR):	20,000,000:1
pixel pitch (H x V):	0.2715 x 0.2715 mm
display area (H x V):	521.3 x 293.2 mm
viewing angle:	horizontal ° x vertical 160° (CR >= 10)
response time:	1 ms
color:	black

SCANNING FREQUENCY

scanning frequency:	horizontal: Hz vertical: 50~76 Hz
---------------------	--------------------------------------

RESOLUTION

max resolution:	1920 x 1080 @ 60 Hz
recommended resolution:	1920 x 1080 @ 60 Hz
color resolution:	16.7 million

POWER

power source:	110-240VAC
power consumption:	ON: <30 W STANDBY: <0.5 W

OTHER FEATURES

user control:	
plug and play:	NA
speakers:	
web cam:	no
headphone out:	NA
wall mount:	NA
height adjustable:	NA
tilt:	-3° ~ 21°

SIGNAL INPUT

analog D-sub 15 pin:	1 x VGA
DVI-D 24-pin:	1 x DVI-D
HDMI:	1 x HDMI
HDMI w/MHL:	0 x HDMI w/MHL
USB 2.0:	0 x USB 2.0
USB 3.0:	0 x USB 3.0
display port (in):	0 x DP (in)
display port (out):	0 x DP (out)
support MHL:	NA

REGULATIONS

Energy Star, CE, FCC, RoHS Compliant, cTUVus

SOFTWARE

e_Saver /

IN THE BOX

HDMI Cable, Power Cord, User Manual, Warranty Card, Driver, AOC Software



MODEL:
E2475SW
J DATA

SHEET

LOADING QUANTITY

20' container loading w/ pallet: 730
40' STD container loading w/ pallet: 1500

DIMENSIONS

product with stand (WxHxD):
558.8mm x 424.6mm x 198.5mm
22" x 16.72" x 7.81"
packaging (WxHxD):
630mm x 418mm x 128mm
24.8" x 16.46" x 5.04"
weight (NET): 3.64 kg | 8.02 lbs
weight (GROSS): 4.05 kg | 8.92 lbs
warranty: 3 years
UPC code: 685417710089