

U70 USB Document Camera

Simple. Powerful. Affordable.



The easiest plug-n-play USB document camera bundled with premium features and pricing has arrived. U70 produces an extraordinary, 4K quality visual experience while still maintaining its simplicity.

Don't miss a pixel

U70's **8MP sensor with 16x digital zoom** delivers best in class pixel performance capturing full resolution that enables vibrant, ultra-clear images.



Smart tools are handy tools

Whether you're doing a live demonstration or livestreaming, leverage U70's **embedded built-in LED and microphone** to enhance the quality of all your visual and audio experiences.



A whole new level of basic

Add the latest USB power and you've got a document camera that super speeds everything to and from its connected device providing a lag-free streaming experience.



Integrate to collaborate

Use U70's **free Sphere2 & ClassSend software** to inspire innovative lesson creation and build classroom engagement. It's the bridge that connects you and your document camera to your students.



Specifications



Image

Sensor	1/3.06" CMOS	Pixel Count	8 megapixels
TV Lines	1400 (8MP) / 1100 (2MP) / 800 (SXGA/720P/XGA)	Frame Rate	60 fps at 720P/1080P, 30 fps at 4K * frame rate could vary depending on computer hardware speed
White Balance	Auto / Manual	Exposure	Auto / Manual
USB Output	3840x2160, 1920x1080, 1280x1024, 1280x720, 1024x768, 800x600, 640x480, 640x360, 320x240		

Optics

Focus	Auto	Shooting Area	Max. 20.8" x 15.5" (530mm x 396mm @ max height) *at 16:9, shooting area 21.4" x 12.0" *at 5:4, shooting area 19.6" x 15.6"
Zooming	16X Digital Zoom		

Button Functions

Snapshot	Take a snapshot onto AVer Software	LED	Turns on the LED light
AF	Initiates the Auto Focus	Rotate	Rotate Image (via AVer software only)
Zoom In	Digitally zoom into image (via AVer software only)	Zoom Out	Digitally zoom out of image (via AVer software only)

Compatibility

Operating Systems	Windows 7 (32/64 bit), Windows 8 (32/64 bit), Windows 10 (32/64 bit), Mac OS X 10.10 or above (Intel based), Chrome OS 29 or above	AVer Software	AVer A+ Software Suite (Sphere 2, PowerPoint Plug-in, Flash-Plug-in), Sphere Lite (for Chromebook)
Interactive Whiteboard Compatibility	Yes with AVerVision Flash Plug-in *certain limitations apply		

Power

Power Source	Powered from USB Connection	Consumption	3.1Watts (lamp on)@USB3.0; 2.5Watts (lamp off)@USB3.0
---------------------	-----------------------------	--------------------	----------------------------------------------------------

Lighting

Lamp Type	LED light
------------------	-----------

Input/Output Connections

USB	USB3.0 (Functions as PC connectivity and Power) * USB2.0 compatibility on Mac OS.	MIC	Built in
------------	--------------------------------------------------------------------------------------	------------	----------

Dimension

Operating	9.1" x 12.2" x 18.4"; 233mm x 312mm x 468mm (+/- 2mm include rubber foot)	Folded	9.5" x 7.3" x 1.7"; 242mm x 187.5mm x 44mm (+/- 2mm include rubber foot)
Weight	3.7 lbs (1.7kg)		

Optional Accessories

Anti-Glare sheet	Part number: PANTIGLA1 (A5 size 8.26" x 5.84")
-------------------------	------------------------------------------------

Package Contents

U70, 4.92'(1.5m) USB3.0 Cable, Warranty Card, Quick Guide

AVER Information Inc. Americas

averusa.com

668 Mission Court,
Fremont, CA 94539

T 408.263.3828

F 408.263.8132

toll free 1.877.528.7824

