

Duplex Singlemode 9/125 Fiber Patch Cable (LC/LC), 7 m (23 ft.)

MODEL NUMBER: **N370-07M**



Premium singlemode fiber optic cabling transmits fast, clear data signals through your LAN with data transfer speeds up to 10 Gbps.

Features

Fast, Clear Data Transmission Through Your LAN

- Data transfer speeds up to 10 Gbps
- Ideal for network equipment that requires singlemode fiber optic patch cables
- Attenuation loss meets or exceeds latest industry standards

Superior Construction for Error-Free Signal Transfer

- 9/125 duplex (zipcord) fiber made from glass
- Sturdy LC male connectors meet stringent insertion loss standards
- Beveled edge on glass ends for easy plug insertion
- Yellow-colored for identification as singlemode

Specifications

| OVERVIEW | |
|--------------|--------------|
| UPC Code | 037332179098 |
| Technology | Singlemode |
| Optical Mode | OS2 |
| PHYSICAL | |
| Color | Yellow |

Highlights

- Attenuation loss meets or exceeds latest industry standards
- 9/125 duplex (zipcord) fiber made from glass
- LC male connectors meet insertion loss standards
- FDDI- and OFNR-rated
- Beveled edge on glass ends for easy plug insertion

System Requirements

- Fiber optic hardware or NIC card requiring singlemode duplex cable with LC/LC connectors

Package Includes

- N370-07M Duplex Singlemode 9/125 Fiber Patch Cable, 7 m



| | |
|-------------------------------------|-----------------------------|
| Cable Jacket Rating | LSZH |
| Clad Diameter | 125 micron |
| Core Diameter | 9 micron |
| Number of Fibers | 2 |
| Cable Length (ft.) | 23 |
| Cable Length (m) | 7 |
| Cable Length (in.) | 275.6 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Weight (kg) | 0.06 |
| Shipping Weight (lbs.) | 0.14 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 to 140 °F (-20 to 60 °C) |
| Storage Temperature Range | -4 to 140 °F (-20 to 60 °C) |
| COMMUNICATIONS | |
| Network Speed | 10Gbps |
| CONNECTIONS | |
| Side A - Connector 1 | LC DUPLEX (MALE) |
| Side A - Connector 2 | LC DUPLEX (MALE) |
| Side B - Connector 1 | LC DUPLEX (MALE) |
| SPECIAL FEATURES | |
| Push/Pull Tabs | No |
| STANDARDS & COMPLIANCE | |
| Approvals | FDDI and OFNR rated |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>