

Processor	Intel® Celeron®, Intel Pentium®, or 6th Generation Intel Core™ i3 / i5 / i7 Processor							<p>Security features</p> <ul style="list-style-type: none"> <li>• Security slot (in rear for optional Kensington® MicroSaver® cable)</li> <li>• Padlock loop</li> <li>• Smart USB protection, allows keyboard/mouse only, blocks all storage devices</li> <li>• Power-on password</li> <li>• Administrator password</li> <li>• Hard disk password</li> <li>• Boot sequence control</li> <li>• Boot without keyboard and mouse</li> <li>• Individual USB port disablement</li> <li>• Chassis intrusion switch</li> </ul> <p>Keyboard</p> <p>Some: Preferred Pro USB Keyboard (USB connector), Lenovo logo</p> <p>Some: Lenovo USB Fingerprint Keyboard (USB connector)</p> <p>Some: Ultrathin Plus Wireless Keyboard (2.4GHz via USB receiver), black</p> <p>Some: Enhanced Optical USB Mouse, black, Lenovo logo</p> <p>Some: Ultrathin Plus Wireless Mouse (2.4GHz via USB receiver), black</p> <p>Mouse</p> <p>Mechanical</p> <p>Tiny (1L), black color; metal case M900 Tiny only: 7.05" W X 7.20" D X 1.36" H 179mm W X 182.9mm D X 34.5mm H 2.9 lb (1.3 kg), weight may vary by configuration With VESA mount &amp; ODD box: 7.42" W X 7.30" D X 2.48" H 188.4mm W X 185.38mm D X 63mm H 4.12 lb (1.87 kg), weight may vary by configuration With VESA mount &amp; I/O box: 7.42" W X 7.30" D X 2.62" H 188.4mm W X 185.38mm D X 66.6mm H 3.53 lb (1.6 kg), weight may vary by configuration Optional VESA mount bracket kit, supports VESA 75mm and 100mm Optional system floor stand for vertical orientation</p> <p>VESA mount Floor Stand</p> <p>Power supply</p> <p>65 watts AC/DC adapter, autosing, 88% PSU (not included for TIO models) 90 watts AC/DC adapter, autosing, 88% PSU (only for models with I/O box)</p> <p>Limited warranty<sup>3</sup></p> <p>Some: 1-year or 3-year, depot service / service upgrades available Some: 1-year or 3-year, limited onsite service / service upgrades available Some: 3-year, limited onsite service, OID (Onsite International Delivery) / service upgrades available For Lenovo service upgrade options, please go to S-TC sheet</p> <p>Preload</p> <p>Preloaded operating system</p> <p>Some: Windows® 7 Professional 64 preinstalled through downgrade rights in Windows 10 Pro 64-bit</p> <p>Some: Windows 7 Professional 64</p> <p>Some: Windows 10 Pro 64-bit</p> <p>Some: Windows 10 Home 64-bit</p> <p>Preloaded applications (only some listed)</p> <ul style="list-style-type: none"> <li>• Desktop Power Manager</li> <li>• Lenovo Solution Center</li> <li>• Lenovo REACHit</li> <li>• Lenovo SHAREit</li> <li>• Lenovo Bluetooth Lock (for models with Wi-Fi/BT card)</li> <li>• McAfee® LiveSafe™ (30-day trial)</li> <li>• Microsoft Office preloaded; purchase a product key to activate</li> <li>• PowerDVD Create (DVD±RW)</li> <li>• Lenovo ThinkVantage Tools</li> <li>• Intel Unite (VPro models only)</li> <li>- Only for Windows 10</li> <li>• Lenovo Companion</li> <li>• Cyberlink PowerDVD (DVD, DVD±RW)</li> <li>• Lenovo QuickOptimizer</li> <li>- Only for Windows 7</li> <li>• Rescue and Recovery</li> <li>• Password Manager</li> <li>• ThinkVantage System Update</li> <li>• Lenovo Message Center Plus</li> <li>• Adobe® Reader®</li> </ul> <p>Environment</p> <p>ENERGY STAR® 6.1*; EPEAT™ Gold rating*; (*Need 85% PSU and Windows OS); ErP Lot 3; GREENGUARD®; RoHS-compliant; TUV Green Mark, ULE Gold</p> <p>Accessories</p> <p>For compatible accessories, please go to TC-AQP sheet</p>	
Memory	32GB max, DDR4 2133, two 260-pin SO-DIMM sockets, dual-channel capable								
Disk	<p>Some: SATA 6.0Gb/s, 2.5" Wide, 5400 rpm or 7200 rpm</p> <p>Some: 500GB (5400 rpm) Solid State Hybrid Drive (SSHD) / with 8GB MLC NAND flash memory, SATA 6.0Gb/s, 2.5" wide</p> <p>Some: Solid State Drive (SSD) / SATA 6.0Gb/s, 2.5" Wide</p>								
Optical	<p>Some: M.2 SSD, PCIe or SATA interface</p> <p>Some: external ODD box with DVD-ROM, 9.5mm high, via USB</p> <p>Some: external ODD box with DVD±RW, 9.5mm high, via USB</p> <p>Some: external ODD box (for TIO) with DVD-ROM, 9.5mm high, via USB</p> <p>Some: external ODD box (for TIO) with DVD±RW, 9.5mm high, via USB</p>								
Onboard SATA Media reader	One SATA cable (1-drop to device), one SATA 6.0Gb/s connector on planar None								
Graphics	Intel HD Graphics 510/530 in processor, uses main memory, DirectX® 12, two DisplayPort™, one optional HDMI, VGA, or 3rd DP, up to 3 independent displays; Max resolution: 4096x2304 (DP) @60Hz; 4096x2160 (HDMI) @24Hz; 1920x1200 (VGA) @60Hz								
DP cable	Optional DP to VGA, DP to DVI-D (single link), or DP to HDMI 1.4 dongle								
Chipset	Intel Q170 Chipset								
Front ports	Two USB 3.0 (one is Always On and fast charge), one microphone (stereo, 3.5mm), one headphone / microphone combo jack (stereo, 3.5mm)								
Rear ports	Four USB 3.0 (optional external optical box or external I/O box occupies one or two specific USB 3.0 on some models), ethernet (RJ-45), two DisplayPort, one optional port (VGA, 3rd DP, HDMI, or serial on some models), one headphone								
I/O box	Optional external I/O box, extends two USB 2.0, two USB 3.0, and one serial on rear, two USB 2.0 on front, via USB (occupy two specific USB 3.0 of M900 Tiny)								
Audio support	High Definition (HD) Audio, Realtek ALC223 / optional internal speaker (1 watt)								
WLAN <sup>13</sup>	<p>Some: 11ac wireless, M.2 Card, Qualcomm Atheros QCA9377 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Qualcomm Atheros QCA6174 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 2x2</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 3165, Wi-Fi + Bluetooth 4.0 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 8260, Wi-Fi + Bluetooth 4.1 combo adapter, 2x2</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 8260, Wi-Fi + Bluetooth 4.1 combo adapter, Intel vPro technology support, 2x2</p>								
Bluetooth™ Ethernet Modem	<p>Some: Bluetooth 4.0 or 4.1 wireless, integrated in Wi-Fi + BT combo adapter</p> <p>Gigabit ethernet, Intel Ethernet Connection I219-LM (Jacksonville), Wake on LAN®</p> <p>None</p>								
Manageability	Intel Active Management Technology 11.0 (Intel AMT 11.0); Intel vPro technology on some models (require choosing a vPro-support Wi-Fi adapter to enable vPro function through wireless connection)								
Security chip	Trusted Platform Module, TCG 1.2-compliant								

<b>Model</b>		<b>10FM000AUS</b>
Product		M900 Tiny
Region		US
Machine Type		10FM
TopSeller		YES
Processor		i5-6500T
Memory		4GBx1
Graphics		Intel HD 530
Storage		120GB SSD
External Optical / I/O box		DVD±RW
WLAN		Intel 8260 ac vPro
Optional Port		HDMI
DP Dongle		None
Chassis Intrusion Switch		Switch
Floor Stand		None
VESA Mount		Mount
Keyboard/Mouse		USB / USB
Internal Speaker		Speaker
Power Supply		65W
Kensington Cable Lock		None
Dust Filter		None
Preload		Windows 7 Pro64 DG Windows 10
Base Warranty (year)		3-onsite
Global (G)		No
Ann Date (mm/yy)		10/15

