

# HP 27er 27-inch Display

Impossibly thin. Irresistibly priced.



Our thinnest LCD display yet<sup>1</sup> has a sleek design that's easy on the eyes. And the crisp, vibrant view from almost any angle comes at an ultra-affordable price.

## Our thinnest LCD display yet<sup>1</sup>


Pushing the limits of thin in an eye-catching design. With our innovative use of high-strength, lightweight metal, we've created our thinnest LCD display yet.<sup>1</sup>

## Stunning from edge to edge

With ultra-wide viewing angles and vivid 1920 x 1080<sup>2</sup> resolution, this edge-to-edge display delivers an expansive entertainment experience for seamless multiple display setups.

## True-to-life color

When the colors on your display are indistinguishable from real life, the result is a beautifully vivid picture. With Technicolor Color Certification, color accuracy is assured every time.



## HP 27er 27-inch Display

<b>Part Number</b>	T3M89AA
<b>Panel Type</b>	27-inch diagonal IPS with low haze
<b>Viewable image area</b>	68,58 cm (27 in) widescreen; diagonally measured
<b>Viewing angle<sup>2</sup></b>	Up to 178° horizontal/ 178° vertical typical
<b>Brightness<sup>2</sup></b>	250 nits
<b>Contrast ratio (typical)<sup>2</sup></b>	1000:1 Static; 5,000,000:1 Dynamic (DCR)
<b>Response rate<sup>2</sup></b>	14ms on/off (typical); 7ms gray-to-gray with overdrive
<b>Color gamut<sup>2</sup></b>	72%
<b>Frequency<sup>2</sup></b>	Horizontal: 30 to 80 kHz; Vertical: 50 to 60 Hz
<b>Aspect ratio<sup>2</sup></b>	16:9
<b>Native resolution</b>	1920 X 1080 @ 60 Hz (Full HD) <sup>1</sup>
<b>Resolutions supported</b>	640 x 480 @ 60Hz, 720 x 400 @ 70Hz, 800 x 600 @ 60Hz, 1024 x 768 @ 60Hz, 1280 x 720 @ 60Hz, 1280 x 800 @ 60Hz, 1280 x 1024 @ 60Hz, 1366 x 768 @ 60Hz, 1440 x 900 @ 60Hz, 1600 x 900 @ 60Hz, 1680 x 1050 @ 60Hz, 1920 x 1080 @ 60Hz
<b>Input signal</b>	VGA, 2 HDMI; HDCP supported on digital input
<b>Cables included</b>	A/C power cable 1,9 m (6.2 ft), Power adapter 1 m (3.2 ft); VGA cable 1.8 m (5.9 ft); HDMI cable 1,8 m (5.9 ft) in selected regions
<b>User controls</b>	Brightness, Contrast, Color Control, Input Control, Image Control, Power Control, Menu Control, Management, Language
<b>Power consumption</b>	Typical: 24 W; Maximum: 29 W; Power Saving: 0.3 W
<b>Dimensions (W x D x H)</b>	Unpacked with stand: 62,09 x 19,45 x 45,56 cm (24.45 x 7.66 x 17.94 in) Head only: 62,09 x 3,56 x 37,16 cm (24.45 x 1.4 x 14.63 in)
<b>Weight</b>	Unpacked with stand: 3,79 kg (8.35 lbs) ; Head only: 3,39 kg (7.46 lbs); Packed: 5,74 kg (12.65 lbs)
<b>Base features</b>	Tilt: -5 to +25 degrees
<b>Color</b>	Front, Neck, and Base: Silver; Back: White
<b>Environmental</b>	Operating: 5° to 35° C (41° to 95° F); Non-operating: -20° to 60° C (-4° to 140° F)
<b>Certification and compliance</b>	ENERGY STAR <sup>®</sup> <sup>3</sup> , EPEAT <sup>®</sup> Silver <sup>4</sup> , CEL Grade 1, Microsoft WHQL Certification (Windows 10), CB, CE, HDMI, TUV-BAUART/ISO9241, CSA/CSA-NRTL, FCC, ICES, S-Mark, VCCI, CCC, China CEL, BSMI, KCC /KC/E-standby, ES7.0 ,EUP Lot 6 and Lot 5 , GEMS, MEPS, UKRAINIA, HRN N NO.201, EAC, IEC60950:1999, IS 1121, SASO, SABS IEC 60950-1, NOM, PSB, ISC, C-Tick , SmartWay Transport Partnership (North America)
<b>Limited warranty</b>	Protected by an HP standard one- or three-year limited warranty (varies by region). Certain restrictions and exclusions apply.

1. FHD (Full High Definition) content required to view HD images.
2. All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
3. ENERGY STAR<sup>®</sup> is a registered trademark of the U.S. Environmental Protection Agency.
4. EPEAT<sup>®</sup> registered where applicable. EPEAT registration varies by country. See [www.epeat.net](http://www.epeat.net) for registration status by country.

### Sign up for updates

[hp.com/go/getupdated](http://hp.com/go/getupdated)

Copyright © 2016 HP Development Company, L.P.

The information contained herein is subject to change without notice. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

