



IPC R2 Mini Rugged PC



Display Outputs	• HDMI (1920 x 1200) • VGA (1920 x 1200) • LVDS (1920 x 1200) • Dual Monitor Capabilities	Shock Protection Standards	• IEC60068-2-27
CPU Support	• Intel Processor J1900, 2M Cache, up to 2.42 GHz, Quad core Processor	Wall Mount	• Custom mounting bracket
I/O Ports	• 2x USB 3.0 Ports • 3x RS232 • 1x RS232/422/485	Networking	• 2x 1Gbps LAN, RJ45, (Realtek 8111G GIGA LAN)
Chipset	• Intel Atom Baytrail-M/D	Expansion Slots	• 2x Mini PCI-e
Memory	• Max 8 GB, DDR3L 1333 MHz, 1 x 204-pin SODIMM	HDD Support	• Removable: 2x 2.5" SATA2 HDD/SSD • Static: Mini-SATA
Operating System	• Windows 10, Windows 8, Windows 7, Linux	Weight	• 5 lbs
Video & Graphics	• Intel HD Graphics	Certifications	• CE, FCC, RoHS, EN50155 & EN50121-3-2
Dimensions	• 10.74" x 6.65" x 2.16" (L, W, D)	Colors	• Aluminum and Blue (Two-Tone)
Audio	• Realtek Audio, 1x Line-out, 3W Audio AMP Output Wafer	Power Supply	• 9~36V wide range input support; Support Standard notebook DC Jack Ø5.5mm x 2.5mm.
Environment	• Ambient Temperature: -25°C ~ 50°C (operating)	Relative Humidity	• 10% ~ 95% (non-condensing)
IEC Vibration Standards	• IEC68-2-64	Wireless	• 802.11 b/g/n & Bluetooth 4.0