

# DATALOCKER SENTRY® 3 FIPS ENCRYPTED FLASH DRIVE



## CONFIDENTLY CARRY DATA EVERYWHERE YOU GO

DataLocker Sentry® 3 FIPS offers advanced security with FIPS 140-2 Level 3 certification and a tamper evident seal for physical security. The entire drive is FIPS certified, not just the controller, and its 256-bit AES hardware-based encryption in XTS mode offers unsurpassed security.

## CENTRALLY MANAGEABLE

This next generation, smart USB 3.0 drive combines 100% hardware encryption with the ability to connect to a remote management console. SafeConsole® is a secure online or on-premise management console to deploy and apply security policies to thousands of USB storage devices easily and efficiently.

## AN EASY AND QUICK WAY TO PROTECT YOUR PORTABLE DATA

Combining password-protected, military-grade encryption with plug-and-play simplicity, DataLocker Sentry® 3 FIPS is the fastest and most secure USB drive in the world.

## AVOID LOSING PUBLIC TRUST

Every year, 20 million unprotected USB drives go missing. If the data stored on those drives ends up in the wrong hands, you can lose public trust, put citizens at risk and suddenly find yourself in the middle of a PR scandal. Secure USB encrypted flash drives offer a safe harbor to data breach notification requirements and are an essential component of a comprehensive data loss prevention (DLP) strategy.

## REQUEST A TRIAL

Request a risk free evaluation unit today: <http://datalocker.com/evaluation/>



## TECHNICAL SPECIFICATIONS

### CAPACITIES<sup>1</sup>

4GB, 8GB, 16GB, 32GB and 64GB

### CRYPTOGRAPHIC PROCESSES

256-bit AES hardware module XTS mode

### TEMPERATURE

Operating: 0°C to 60°C

Storage: -20°C to 85°C

### DIMENSIONS (L X W X D)

77.9 mm x 22.2 mm x 12.05mm

### WEIGHT

Approximately 54 grams (1.9 oz)

### COUNTRY OF ORIGIN

USA

### INTERFACE

USB 3.0 – Backward compatible w/ USB 2.0 & 1.1

### STANDARDS & CERTIFICATIONS

TAA Compliant, FCC, CE, VCCI & KC, RoHS & WEEE

### SYSTEM COMPATIBILITY

Windows® 10, 8.1, 8, 7 (SP1), Windows Vista® (SP2), Mac OS X v.10.7.x -10.11.x

Two (2) free drive letters required for use

### SPEED<sup>2</sup>

USB 3.0: 4GB: 80MB/s read, 12MB/s write  
 8GB & 16GB: 165MB/s read, 22MB/s write  
 32GB: 250MB/s read, 40MB/s write  
 64GB: 250MB/s read, 85MB/s write  
 USB 2.0: 4GB: 30MB/s read, 12MB/s write  
 8GB-64GB: 30MB/s read, 20MB/s write

### WATERPROOF

Up to 4ft; Conforms to IEC 60529 IPX8. Product must be clean and dry before use.

### WARRANTY

2 year limited

## SALES CONTACTS

### WEBSITE

[datalocker.com](http://datalocker.com)

### EUROPE

[emea@datalocker.com](mailto:emea@datalocker.com)

### US AND CANADA

[sales@datalocker.com](mailto:sales@datalocker.com)  
 +1 913 310 9088

### ASIA PACIFIC

[apac@datalocker.com](mailto:apac@datalocker.com)

<sup>1</sup> Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products.

<sup>2</sup> Speed may vary due to host hardware, software and usage.