



**KBA-CK104S-WNUN-US** White, USB  
**KBA-CK104S-BNUN-US** Black, USB

**Key Features:**

- 104 keys
- Stands up to most common hospital grade disinfectant chemicals
- Sealed
- Wrapped in silicone skin: rated IP68
- Scissors balancing key guidance with contained contact system
- Compact notebook style layout with VESA mounting holes on the bottom
- LED status indicators: Caps Lock, Num Lock, Scroll Lock, Clean Function

**Electronics:**

- Voltage: 5Vdc from data cord
- Current Input: 100 mA max

**Interfaces:**

- USB 2.0 Type A

**Mechanical:**

- Number of keys: 104
- Key strokes life: 10 million

**Other:**

- Dimensions: 449 x 142 x 26 mm
- Temperature:  
Storage: -40 to +70 C  
Operation: 0 to +70 C

**Cleaning Instructions:**

- Fn + Shift (Clean on/off)
- "Clean" LED will illuminate, indicating cleaning mode
- To turn off, repeat step 1
- "Clean" LED will turn off, indicating typing mode