


XMP-6200

1080p Solid-State Network Media Player




Embrace the multimedia age with the XMP-6200 Media Player. Feature dynamic and engaging digital signs in designed locations to deliver customized information or advertisement instantly.



Effortless Setup

Setting up the XMP-6200 couldn't be easier. Simply power up the device and you are ready to go. Previous technology experience is not necessary, which reduces overall set up costs.



Easy and Flexible Usability

So much power is packed into such a small form factor. The XMP-6200 content management is centralized and remote. You can control playback schedule as well as turn on and off display all from your fingertips.



Minimal Maintenance

The robust XMP-6200 is designed for 24/7 usage with self-recovery mechanism and a fanless cooling system for minimal maintenance and maximum running time.

Technical Specification

Open Standards Supported

- HTML5, JavaScript, and CSS
- Android 4.4 API
- W3C SMIL for cross-platform management
- W3C Widgets for HTML delivery
- POPAI Digital Signage Content Standards, including:
 - S1 (JPEG 480p baseline)
 - S2 (JPEG 720p baseline)
 - S4 (MPEG L2 audio)
 - S5 (MP3 audio, 384Kbps)
 - S6 (MPEG-1 SIF, 3Mbps CBR)
 - S7 (MPEG-1 480p, 10Mbps CBR)
 - S8 (MPEG-1 720p, 15Mbps CBR)
 - S9 (MPEG-2 480p, 6Mbps CBR)
 - S10 (MPEG-2 720p, 12Mbps CBR)
 - S11 (H.264/MPEG-4 AVC, 480p, 6Mbps CBR)
 - S12 (H.264/MPEG-4 AVC, 720p, 10Mbps CBR)
 - E1 (PNG 24bpp+alpha, 480p)
 - E2 (PNG 24bpp+alpha, 720p)
 - E4 (VC-1/WMV9, MP@ML, 720p)
 - E7 (MPEG-4 ASP, 480p, 10Mbps CBR)
 - E8 (H.264/MPEG-4 AVC, 1080p, 20Mbps CBR)

Advanced Signage Features

- Remote commissioning
- AlwaysOn, AppLock to prevent unauthorized access
- StrongCache for continued playback even when network is not available

HTML5 Support

- Widgets for calendar, clock, news, weather, Twitter, and web page integration
- HTML5 technologies including CSS and Javascript
- WebKit-based browser engine, same as Google Chrome™ and Apple Safari® browsers

Digital Signage Features

- Multi-zone screen layout, transparent PNG overlay, and graphical scrolling ticker
- Auto-play starts playing scheduled contents automatically when power is re-established
- Automatic error recovery with built-in WDT
- Real-time clock with backup clock battery

Content Management

- SignApps Express Utility
- 3rd party solution (optional license)

Connectivity

- Wi-Fi: 802.11 b/g/n
- HDMI 1.4 (Full-HD 1080p with audio)
- Micro USB for ADB
- Ethernet 10/100 BASE-T
- USB 2.0 x 2
- Optional 3G/4G mobile module via USB

Local Storage

- 8 GB flash memory (approx. 360 minutes of typical 720p video @3 Mbps)
- Micro SD card slot (support up to 32GB storage)

Mounting kit

- Built-in VESA compatible 100x100(mm)

Supplied accessories

- HDMI cable
- External 5dB Wi-Fi antenna
- Velcro

Expansion Options

- 16GB/32GB micro SD/SDHC memory card

AC Adapter

- Input: 100-240V, 50-60 Hz, 0.5A Max.
- Output: 12V, 1.5A
- UL/FCC/CE/CCC/C-Tick/VCCI certified power supplies
- Interchangeable connector system includes US plugs (Option for EU, UK and AUS plugs)

Environmental

- Operating temperature: 0 to 45°C
- Humidity: 10 to 85% @ 40°C, non-condensing

Dimensions for Product and Package

- Size: 167 mm x 118.8 mm x 24.5 mm / 6.57" x 4.67" x 0.96"
- Weight: 275 g / 0.61 lbs.
- Individual Package Size:
225.5mmx168mmx79mm/8.88"x6.61"x3.11"
- Outer Carton Size:
480mmx425mmx387mm/18.89"x16.73"x15.23"
- Units per Outer Carton: 20

Certifications

- CE/FCC/VCCI/TELEC/CCC/IC

Warranty

- 1-year limited parts & labor

Product Photos



Retail advertisement demo
(Monitor not included)

Contact

IAdea Corporation (Headquarters)
3F, No. 21, Lane 168, Xingshan Road
Taipei, Taiwan 114
Phone: +886-2-2791-1110
Fax: +886-2-2791-1170
Email: Sales@IAdea.com
Website: <http://www.IAdea.com>

IAdeaAmerica Corp.
20 Fairbanks, Suite 170
Irvine, CA 92618
Tel: +1-949-305-6489
Email: US-Sales@IAdea.com

Authorized Reseller

