



P705G TIER 1 ADVANCED POWER STRIP

Safeguard your equipment from damaging power transients and help lower your electric bill.

The CyberPower P705G is a commercial and residential surge protector for personal computers, large flat screen TVs, printers, speakers, scanners and home electronics. It offers seven (7) total surge protected outlets and four (4) Energy-Saving outlets designed to turn off up to four connected devices when your TV or PC is shut down or goes into standby mode. The Energy-Saving Threshold Switch keeps the energy-saving feature active when the Master Outlet detects low power consumption.

The P705G features 2100 Joules of protection and metal oxide varistor (MOV) technology, which guards the surge suppressor and connected electronics against line abnormalities and lightning surges. EMI/RFI filters block unwanted line noise from all connected electronics.

Our Flame Resistant Technology uses an ABS housing that provides a high level of protection (UL 94 Recognized V-Oclass material).

A Limited Lifetime Warranty ensures that this surge suppressor has passed our highest quality standards in design, assembly, material, and workmanship; further protection is offered by a \$250,000 Connected Equipment Guarantee.

SPECIFICATIONS

INPUT	
Circuit Breaker	15 Amp
Plug Type	NEMA 5-15P
Plug Style	Right Angle
Cord Length	5'
OUTPUT	
Outlet Type	NEMA 5-15R
Outlets - Total	7
Outlets - Energy Saving	4
Outlets - Always On	2
Outlets - Widely Spaced	1

TYPICAL APPLICATIONS

- Consumer Electronics
- Energy-Saving
- Home Theater Equipment
- Personal Computers
- Phone/Fax/Modem
- Printers

FEATURES

- 7 Surge Protected Outlets
- 4 Energy-Saving Outlets
- 1 Control/Master Outlet
- 2 Always On Outlets
- Energy-Saving Threshold Switch
- 2100 Joules of Surge Protection
- Flame Resistant Technology
- 5 ft. Cord
- Lifetime Warranty



SURGE PROTECTION & FILTERING	
Surge Suppression	2,100 Joules
Threshold Switch	High/Low
Maximum Surge Current	105,000 Amps
Maximum Surge Current H-N	45,000 Amps
Maximum Surge Current H-G	30,000 Amps
Maximum Surge Current N-G	30,000 Amps
Clamping Voltage	400V (L-N, L-G, N-G)
Response Time	< 1 nanosecond
EMI/RFI Filtration	Yes
Attenuation	Up to 32dB

P705G

TIER 1 ADVANCED POWER STRIP

SPECIFICATIONS CONT.

PHYSICAL	
Safety Covers	Yes
Keyhole Mounting Slots	Yes
Dimensions - Width/Height/Depth (in.)	2.76 x 1.34 x 12.09 in.
Weight (lb)	1.26 lb.
CERTIFICATIONS	
Safety	cUL UL1363 UL1449 3rd Edition
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	Lifetime
Connected Equipment Guarantee	Lifetime
CEG Amount	\$250,000