

ThinkCentre M700 SFF Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Celeron®, Intel Pentium®, or 6th Generation Intel Core™ i3 / i5 / i7 Processor						Security features - One lock to secure both cover and entire system to fixed object: -Padlock loop (in rear for opt padlock) -Security slot (in rear for optional Kensington® MicroSaver® cable) - Optional cable lock to physically lock both keyboard and mouse - Power-on password - Administrator password - Hard disk password - Boot sequence control - Boot without keyboard and mouse - Individual USB port disablement - Optional chassis intrusion switch
	Processor	Cores / Threads	Frequency Base/Max(GHz)	Cache	Memory Types	Integrated Graphics	
	Celeron G3900	2 / 2	2.8 G	2 MB	DDR4-2133	HD 510	
	Pentium G4400	2 / 2	3.3 G	3 MB	DDR4-2133	HD 510	
	Pentium G4500	2 / 2	3.5 G	3 MB	DDR4-2133	HD 530	
	Core i3-6100	2 / 4	3.7 G	3 MB	DDR4-2133	HD 530	
	Core i3-6300	2 / 4	3.8 G	4 MB	DDR4-2133	HD 530	
	Core i5-6400	4 / 4	2.7 G / 3.3 G	6 MB	DDR4-2133	HD 530	
	Core i5-6500	4 / 4	3.2 G / 3.6 G	6 MB	DDR4-2133	HD 530	
	Core i5-6600	4 / 4	3.3 G / 3.9 G	6 MB	DDR4-2133	HD 530	
	Core i7-6700	4 / 8	3.4 G / 4.0 G	8 MB	DDR4-2133	HD 530	
Memory	32GB max, UDIMM, DDR4 2133, two 288-pin DIMM sockets, dual-channel capable						Keyboard - Some: PS/2 Keyboard (PS/2 connector), Lenovo logo - Some: Preferred Pro USB Keyboard (USB connector), Lenovo logo - Some: Lenovo USB Fingerprint Keyboard (USB connector) - Some: Ultralim Plus Wireless Keyboard (2.4GHz via USB receiver), black - Some: PS/2 Optical Wheel Mouse, black, Lenovo logo - Some: Enhanced Optical USB Mouse, black, Lenovo logo - Some: Ultralim Plus Wireless Mouse (2.4GHz via USB receiver), black Mouse <

See footnotes for more detailed information

Model	10GT002MUS
Product	ThinkCentre M700 SFF
Region	US
Machine Type	10GT
TopSeller	TopSeller
Processor	Core i7-6700 (4C, 3.4 / 4.0GHz, 8MB)
vPro	No
Graphics	Integrated Intel HD Graphics 530
Monitor Cable	None
Memory	8GBx1
Storage	1TB 7200rpm 3.5"
Optical	DVD±RW
Optional 2nd 2.5" Bay	None
Media Reader	None
WLAN + Bluetooth	Intel 8260 ac, 2x2 + BT4.1
Optional Front Ports	None
Optional Rear Ports	None
Chassis Intrusion Switch	None
Cable Lock	None
Dust Filter	None
Keyboard / Mouse	USB / USB
Stand	Floor Stand
Power Supply	210W 85%
Operating System	Windows 10 DG Windows 7 Pro 64
Warranty	3-year, Onsite
Global	No
Ann Date (mm/yy)	01/16

