


ThinkCentre M700 SFF Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Celeron®, Intel Pentium®, or 6th Generation Intel Core™ i3 / i5 / i7 Processor						Security features	- One lock to secure both cover and entire system to fixed object: -Padlock loop (in rear for opt padlock) -Security slot (in rear for optional Kensington® MicroSaver® cable) - Optional cable lock to physically lock both keyboard and mouse	- Power-on password - Administrator password - Hard disk password - Boot sequence control - Boot without keyboard and mouse - Individual USB port disablement - Optional chassis intrusion switch
	Processor	Cores / Threads	Frequency Base/Max(GHz)	Cache	Memory Types	Integrated Graphics			
	Celeron G3900	2 / 2	2.8 G	2 MB	DDR4-2133	HD 510			
	Pentium G4400	2 / 2	3.3 G	3 MB	DDR4-2133	HD 510			
	Pentium G4500	2 / 2	3.5 G	3 MB	DDR4-2133	HD 530			
	Core i3-6100	2 / 4	3.7 G	3 MB	DDR4-2133	HD 530			
	Core i3-6300	2 / 4	3.8 G	4 MB	DDR4-2133	HD 530			
	Core i5-6400	4 / 4	2.7 G / 3.3 G	6 MB	DDR4-2133	HD 530			
	Core i5-6500	4 / 4	3.2 G / 3.6 G	6 MB	DDR4-2133	HD 530			
	Core i5-6600	4 / 4	3.3 G / 3.9 G	6 MB	DDR4-2133	HD 530			
	Core i7-6700	4 / 8	3.4 G / 4.0 G	8 MB	DDR4-2133	HD 530			
Memory	32GB max, UDIMM, DDR4 2133, two 288-pin DIMM sockets, dual-channel capable						Mechanical	- SFF (9.7L), black color; metal case (WxDxH) 13.31" X 14.05" X 3.46"; 338mm X 357mm X 88mm 12.3 lb (5.6 kg) - Toolless cover, disk, optical removal - Toolless graphics, PCI adapter retention - Optional dust filter Bay 1: N/A, 9.5mm high, external, std optical Bay 2: 3.5", 1" high, internal, std disk Bay 3: 2.5", N/A, internal, opt 2nd 2.5" disk (optional bay) Bay 4: N/A, N/A, external, opt reader Slot 1: Low Profile, PCI Express 3.0 x16 Slot 2: Low Profile, PCIe 2.0 x1 Slot 3: Low Profile, PCIe 2.0 x1 Optional system floor stand for vertical orientation	
Disk	<i>Some:</i> Hard disk, SATA 6.0Gb/s, 2.5" / 3.5" wide, 5400 / 7200 rpm <i>Some:</i> Solid State Hybrid Drive (SSHD), 500GB (5400 rpm, 2.5") / 1TB or 2TB (7200 rpm, 3.5"), with 8GB NAND flash memory, SATA 6.0Gb/s <i>Some:</i> Solid State Drive (SSD) / SATA 6.0Gb/s, 2.5" Wide								
Optical	<i>Some:</i> DVD-ROM SATA 1.5Gb/s Drive <i>Some:</i> Super Multi-Burner DVD±RW SATA 1.5Gb/s Drive								
Onboard SATA	Three onboard SATA 6.0Gb/s connectors								
Media reader	Optional 9-in-1 media reader								
Graphics	Intel HD Graphics 510/530 in processor, uses main memory, DirectX® 12, one VGA, one DisplayPort™, supports two independent displays, works along with discrete graphics to support more displays; <i>Max resolution:</i> 4096x2304 (DP)@60Hz; 1920x1200 (VGA)@60Hz <i>Some:</i> NVIDIA® Quadro® K420 , DirectX 12, 2GB, PCIe 2.0 x16 adapter, one DVI-I, one DisplayPort, 41 watts; <i>Max resolution:</i> 3840x2160 (DisplayPort)@60Hz; 2560x1600 (DVI-I)@60Hz <i>Some:</i> NVIDIA GeForce® GT 720 , DirectX 12, 2GB, PCIe 2.0 x8 adapter, one VGA, one HDMI, 25 watts; <i>Max resolution:</i> 1920x1080 (HDMI)@60Hz; 2048x1536 (VGA)@85Hz <i>Some:</i> NVIDIA GeForce GT 720 , DirectX 12, 1GB, PCIe 2.0 x8 adapter, two DisplayPort, 25 watts; <i>Max resolution:</i> 3840x2160 (DisplayPort)@60Hz;								
DP cable	Optional DP to VGA, DP to DVI-D (single link), or DP to HDMI 1.4 dongle								
Chipset	Intel H110 Chipset								
Front ports	Two USB 3.0, two optional USB 2.0, microphone (3.5mm), headphone (3.5mm)								
Rear ports	Two USB 3.0, two USB 2.0, two optional USB 2.0, serial (9-pin), optional 2nd serial (9-pin), optional parallel (25-pin), ethernet (RJ-45), one VGA, one DisplayPort, two PS/2 ports (keyboard/mouse); additional VGA, DisplayPort, DVI-I or HDMI on optional graphics on some models								
Rear audio ports	Line-in (3.5mm), line-out (3.5mm), microphone-in (3.5mm)								
IEEE 1394	None								
Audio support	High Definition (HD) Audio, Realtek ALC662 / optional internal speaker (1.5 watt)								
WLAN ¹³	<i>Some:</i> 11ac wireless, M.2 Card, Qualcomm Atheros QCA9377 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 1x1 <i>Some:</i> 11ac wireless, M.2 Card, Qualcomm Atheros QCA6174 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 2x2 <i>Some:</i> 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 3165, Wi-Fi + Bluetooth 4.0 combo adapter, 1x1 <i>Some:</i> 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 8260, Wi-Fi + Bluetooth 4.1 combo adapter, 2x2								
Bluetooth™	<i>Some:</i> Bluetooth 4.0 or 4.1 wireless, integrated in Wi-Fi + BT combo adapter								
Ethernet	Gigabit ethernet, Realtek RTL8111GN, Wake on LAN®								
Modem	None								
Manageability	None								
Security chip	Trusted Platform Module, TCG 1.2-compliant								

Environment	ENERGY STAR® 6.0*, EPEAT™ Gold rating* (*Need 85% PSU and Windows OS); ErP Lot 3; GREENGUARD®; RoHS-compliant
Accessories	For compatible accessories, please go to TC-AQP sheet

See footnotes for more detailed information

Model	10GT0028++
Product	ThinkCentre M700 SFF
Region	WE
Machine Type	10GT
TopSeller	TopSeller
Processor	Core i3-6100 (2C, 3.7GHz, 3MB)
vPro	No
Graphics	Integrated Intel HD Graphics 530
Monitor Cable	None
Memory	4GBx1
Storage	500GB 7200rpm 3.5"
Optical	DVD±RW
Optional 2nd 2.5" Bay	None
Media Reader	9 in 1
WLAN + Bluetooth	None
Optional Front Ports	None
Optional Rear Ports	Parallel
Chassis Intrusion Switch	Chassis Intrusion Switch
Cable Lock	None
Dust Filter	None
Keyboard / Mouse	USB / USB
Stand	None
Power Supply	210W 85%
Operating System	Windows 10 DG Windows 7 Pro 64
Warranty	3-year, Onsite
Global	No
Ann Date (mm/yy)	01/16

