



QCA8045B

Camera Type	Bullet
Camera Technology	Analog HD
Image Sensor Size	1/2.7"
Image Sensor Type	CMOS
Image Resolution	1080P High Definition
Megapixels (digital)	2
Effective Pixels	1930x1088
Lens Size	3.6mm
Angle of View	65 to 70
IR Cut Filter	Yes



NIGHT VISION

IR LEDs	24
Infrared Wavelength	850nm
Min Lux Illumination	0.01/F1.2(color), w/AGC on, 0Lux IR on
Night Vision Range	Up to 80 ft

ADDITIONAL IMAGE FEATURES

Auto Iris	No
On Screen Display	No
Backlight Compensation	Yes
Electronic Shutter	1/60-1/100,000s
Gain Control	Auto
Wide Dynamic Range	No
Noise Reduction	2D-DNR

REMOTE MONITORING

Use as Standalone	No
Compatible Mobile Devices	None, depends on DVR connected to
Compatible Systems	QC AnalogHD DVRs

PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP66
Body Construction	Metal
Mounting Hardware	Screws
Weight	14 oz
Dimensions without bracket	2.5" w x 3.25" d x 2.5" h
Dimensions with bracket	2.5" w x 6.25" d x 2.5" h
Operating Temperature	-22° to 122° F

PTZ

Horizontal Rotation	Not applicable
Vertical Tilt	Not applicable
Preset and Cruise Patterns	Not applicable

AUDIO

Audio Range	Not applicable
Audio Microphone	Not applicable

CONNECTIVITY

Connector Types	BNC
Other Connections	2.1mm power
Wireless	No

POWER

Power Supply	12V 300mA
Power Consumption	<3.6W (LEDs ON)