

# ideapad Y700 Platform Specifications

Product Specifications Reference (PSREF)

Processor	6th Generation Intel® Core™ i5 / i7 Processors								Media reader Ports	4-in-1 reader (SD, SDXC, SDHC, MMC) USB 3.0 x 2, USB 2.0 x 1 (for power charge), HDMI, Ethernet (RJ-45), audio combo jack																								
	<table border="1"> <thead> <tr> <th>Processor Number</th><th># of Cores</th><th># of Threads</th><th>Base Frequency</th><th>Max Turbo Frequency</th><th>Cache</th><th>Memory Speed</th><th>Processor Graphics</th></tr> </thead> <tbody> <tr> <td>i5-6300HQ</td><td>4</td><td>4</td><td>2.3 GHz</td><td>3.2 GHz</td><td>6MB</td><td>DDR4-2133MHz</td><td>Intel HD Graphics 530</td></tr> <tr> <td>i7-6700HQ</td><td>4</td><td>8</td><td>2.6 GHz</td><td>3.5 GHz</td><td>6MB</td><td></td><td></td></tr> </tbody> </table>									Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Speed	Processor Graphics	i5-6300HQ	4	4	2.3 GHz	3.2 GHz	6MB	DDR4-2133MHz	Intel HD Graphics 530	i7-6700HQ	4	8	2.6 GHz	3.5 GHz	6MB			Some: 720p HD, 1.0MP resolution, fixed focus, dual array microphone Some: Intel 3D camera, dual array microphone
Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Speed	Processor Graphics																											
i5-6300HQ	4	4	2.3 GHz	3.2 GHz	6MB	DDR4-2133MHz	Intel HD Graphics 530																											
i7-6700HQ	4	8	2.6 GHz	3.5 GHz	6MB																													
Max resolution: 3840x2160@30Hz (HDMI)									HD audio, JBL stereo speakers with Dolby® Home Theater, 2W x 2 / optional 3W subwoofer, dual array microphone, combo audio / microphone jack																									
Graphics	Some: NVIDIA® GeForce® GTX 960M, 2GB or 4GB memory, DirectX 12 Some: AMD Radeon™ R9 M375, 2GB or 4GB memory, DirectX 12								Keyboard	Full-size keyboard, 6-row, multimedia Fn keys, Novo button (Novo key), optional backlight, optional numeric keypad																								
Chipset Memory	Intel HM170 Chipset 16GB max / PC4-17000 2133MHz DDR4, non-parity, dual-channel capable, two 260-pin SO-DIMM sockets								Touchpad	One-piece multi-touch touchpad																								
Display	Some: 14.0" (356mm) FHD (1920x1080) color, IPS, LED backlight, 250 nits, 16:9 aspect ratio, 600:1 contrast ratio Some: 15.6" (396mm) FHD (1920x1080) color, IPS, LED backlight, 250 nits, 16:9 aspect ratio, 600:1 contrast ratio Some: 15.6" (396mm) UHD (3840x2160) color, IPS, LED backlight, 300 nits, 16:9 aspect ratio, 1000:1 contrast ratio Some: 17.3" (439mm) FHD (1920x1080) color, IPS, LED backlight, 300 nits, 16:9 aspect ratio, 700:1 contrast ratio								Security	Power-on password, hard disk password, supervisor password, security keyhole																								
Multi-touch	Optional: Capacitive-type multi-touch, supports 10-point, One Glass Solution								Security chip	None																								
SATA disk	Some: HDD / 2.5" wide, 7mm high Some: Hybrid drive with 8GB NAND flash memory / 2.5" wide, 7mm high								Fingerprint reader	None																								
M.2 SSD (opt) SATA controller Optical	M.2 Solid State Drive (SSD), via M.2 card slot Serial ATA, SATA 6.0Gb/s support, integrated in chipset Some: External optical box with DVD±RW, 9.5mm high, tray-in, via USB 2.0 Some: External optical box with Blu-ray burner, 9.5mm high, tray-in, via USB 2.0								Battery type	Some: integrated Li-Polymer 3-cell (45Wh) battery Some: integrated Li-Polymer 4-cell (60Wh) battery																								
Ethernet WLAN	One of the following, configurable by model: 11ac+BT: 11ac, 1x1, Wi-Fi + Bluetooth combo adapter, M.2 Card Intel 3165 ac+BT: 11ac, 1x1, Intel Dual Band Wireless-AC 3165, Wi-Fi + Bluetooth combo adapter, M.2 Card Intel 8260 ac+BT: 11ac, 2x2, Intel Dual Band Wireless-AC 8260, Wi-Fi + Bluetooth combo adapter, M.2 Card								Battery life	Some: up to 5hrs Some: up to 7hrs (run mobilemark2014)																								
WWAN Bluetooth™	None Bluetooth 4.1 wireless, integrated in Wi-Fi + Bluetooth combo adapter								AC adapte	135-watt AC adapter																								
Dimensions	Some: WxDxH: 13.78" x 10.2" x 1.02"; 350mm x 259mm x 26mm Some: WxDxH: 15.23" x 10.9" x 1.02"; 387mm x 277.5mm x 25.95mm Some: WxDxH: 15.23" x 10.9" x 1.09"; 387mm x 277.5mm x 27.7mm Some: WxDxH: 16.65" x 12.0" x 1.10"; 423mm x 305mm x 27.95mm								Limited warranty	1 year depot limited warranty / service upgrades available																								
Weight	14.0" models: 2.2kg (4.85lb) with 3-cell battery 15.6" models: 2.6kg (5.73lb) with 4-cell battery 17.3" models: 3.5kg (7.72lb) with 4-cell battery								Preload	Windows® 10 Home 64 Preloaded applications (only some listed) <ul style="list-style-type: none"><li>Lenovo® Photo Master 2.0</li><li>Lenovo SHAREit</li><li>Lenovo Companion</li><li>Lenovo Solution Centre</li><li>McAfee® LiveSafe™ (30-day trial)</li><li>Microsoft Office preloaded; purchase a product key to activate</li></ul>																								
Case color Case material	Top: black; bottom: black Some: top: PC-ABS, texture with painting; bottom: PC-ABS, texture with painting Some: top: aluminium, coress hairline; bottom: aluminium, coress hairline								Environment	EPEAT™ Silver; ENERGY STAR® 6.1; RoHS-compliant																								

<b>Model</b>		<b>80Q0001MUS</b>
Product		ideapad Y700-17ISK
Region		US
Machine Type		80Q0
Processor		Core i7-6700HQ (4C, 2.6 / 3.5GHz, 6MB)
Graphics		NVIDIA GeForce GTX 960M 4GB GDDR5
Chipset		Intel HM170
Memory		8GBx1
Display		17.3" FHD (1920x1080) IPS Anti-glare
Multi-touch		None
Storage		1TB 5400rpm + 128GB SSD M.2
Optical		None
Ethernet		100/1000M
WLAN + Bluetooth		Intel 3165 ac, 1x1 + BT4.1
Color		Black, Metal
Camera		1.0MP
Microphone		Dual Array
Keyboard		Backlit
Fingerprint Reader		None
Battery		4-cell (60Wh)
Power Adapter		135W
Operating System		Windows 10 Home 64
Warranty		1-year, Depot
Ann Date (mm/yy)		10/15



