

Lenovo Flex 4 (15 inch) Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Pentium® Processor or 6th Generation Intel Core™ i3 / i5 / i7 Processor								Media reader	4-in-1 reader (MMC, SD, SDHC, SDXC)
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics	Ports	Two USB 3.0, one USB 2.0 (Always On), HDMI, Ethernet (RJ-45)
	Pen 4405U	2	4	2.1 GHz	-	2MB	DDR4-2133	Intel HD Graphics 510	Dimensions	WxDxH: 14.88" x 9.96" x 0.84"; 378mm x 253mm x 21.35mm
	i3-6100U			2.3 GHz	-	3MB		Intel HD Graphics 520	Weight	2.08 kg (4.59 lb)
	i5-6200U			2.3 GHz	2.8 GHz	3MB			Case color	Black, Silver, Red, or Purple
	i7-6500U			2.5 GHz	3.1 GHz	4MB			Case material	Display cover: PC + 30%GF Bottom: PC/ABS plastic
Graphics	Intel HD Graphics 510 or 520 in processor only, or Intel HD Graphics 520 in processor and AMD Radeon R7 M460, 2GB memory; supports dual independent display Max resolution: 4096x2160@24Hz (HDMI)								Camera	HD720p, fixed focus, integrated dual array microphone
Chipset	Intel SoC (System on Chip) platform 16GB max ⁷ / 2133MHz DDR4, dual-channel capable, one DDR4 SO-DIMM socket								Audio support	HD Audio, dual array microphone, combo audio / microphone jack
Memory									Keyboard	6-row, multimedia Fn keys, optional LED backlight
Display	15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, 250 nits, 16:9 aspect ratio, IPS Capacitive-type multi-touch, supports 10-point, OGS 360° rotation hinge supports four distinct modes (Laptop, Stand, Tent & Tablet) Accelerometer (G) sensor, supports 3-axis accelerometer								Touchpad	One-piece multi-touch touchpad
Multi-touch									Security	Power-on password, hard disk password, supervisor password, security keyhole
Hinge	Serial ATA, SATA 6.0Gb/s support, integrated in processor								Security chip	None
G-sensor									Fingerprint reader	None
Storage	Some: SSD / SATA 6.0Gb/s, 2.5" wide, 7mm high Some: HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high Some: SSHD with 8GB NAND flash memory								Battery	Integrated Li-Polymer 3-cell (52.5Wh) battery
SATA controller									Max battery life ¹⁰	Up to 9hr
Optical	None								AC adapter	65W AC adapter
Ethernet									Preload	Windows® 10 Home 64 • Lenovo Solution Center • Lenovo® OneKey® Recovery • Lenovo SHAREit • Lenovo REACHit • Lenovo Photo Master • McAfee® LiveSafe™ (30-day trial) • Microsoft Office preloaded; purchase a product key to activate
WLAN	Gigabit Ethernet connection								Limited warranty	1-year depot repair service
Bluetooth™									Environment	EPEAT™ Silver; ENERGY STAR® 6.1; RoHS-compliant

Model	80SB0001US
Product	Lenovo Flex 4-1570
Machine Type	80SB
Region	US
Processor	Core i7-6500U (2C, 2.5 / 3.1GHz, 4MB)
Graphics	Integrated Intel HD Grahpics 520
Memory	8GBx1
Display	15.6" FHD (1920x1080) IPS
Multi-touch	10-point Multi-touch
Storage	500GB 5400rpm
Optical	None
Ethernet	100/1000M
WLAN + Bluetooth	11ac, 2x2 + BT4.0
Color	Black
Camera	720p
Keyboard	Backlit
Fingerprint Reader	None
Battery	3-cell (52.5Wh)
Power Adapter	65W
Operating System	Windows 10 Home 64
Warranty	1-year, Depot
Ann Date (mm/yy)	03/16

L
LAPTOP



TENT



Z
STAND



TABLET



