



AG271QG

68.6cm (27") LCD MONITOR

27-inch IPS display with NVIDIA G-SYNC technology, lightning-fast 165Hz refresh rates and unique ergonomic base for high-performance gaming



ADJUSTABLE



AUDIO



USB 3.0



HDMI



SWIVEL



HEADPHONE OUT



USB CHARGER



DISPLAYPORT

GENERAL FEATURES

Line	AOC Gaming
Panel Type	IPS technology
Panel Size	27" / 68.6 cm
Aspect Ratio	16:9
Brightness	350 cd/m²
Contrast Ratio Dynamic	50M:1
Contrast Ratio Static	1000:1
Pixel Pitch(H) (V)	0.2331
Display Area (H x V)	596.74 x 335.66
Viewing Angle (CR >= 10)	178/178
Response time	4ms GTG
Color	Black Red

SCANNING FREQUENCY

Scanning Frequency	H=30~165KHz (DP)/ 30~83KHz (other), V=30~165Hz (DP)/ 50~76Hz (other)
--------------------	---

RESOLUTION

Maximum Resolution	2560x1440@165Hz
Recommended Resolution	2560x1440@165Hz
Colors	16.7 Million
HDCP compatible	Yes

CONNECTORS

D-Sub	-
DVI	-
HDMI	1x
USB	4x USB 3.0
MHL	-
DisplayPort	1x

POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 45W, Standby: 0.5W, Off: 0.5W
Zero Power Switch	-

OTHER FEATURES

Plug and play	Yes
Kensington Lock	Yes
Vesa Wallmount	100x100
FlickerFree	Yes
Speakers	2W
Regulations	Energystar 6 TCO certified

ACCESSORIES

HDMI Cable
Displayport Cable
Audio Cable
USB 3.0 Cable
Power Schuko C5 Cable

ERGONOMIC DATA

Pivot	Yes
Swivel	-20/20
Tilt	-3.5/21.5
Height Adjustment	130mm

DIMENSIONS

Product with stand (W×H×D)	623x433x218 mm
Packaging (W×H×D)	715x240x480 mm
Weight	6.8 kg wo/packaging 10 kg w/packaging
Warranty	3 Years
EAN	4038986185844