

USB 2.0 A/B Coiled Cable (M/M), 6 ft. (1.83 m)

MODEL NUMBER: **U022-006-COIL**



Connects high-speed USB 2.0 peripherals with a USB-B port to your computer, laptop or other compatible USB-A device. Ideal for printers and scanners.

Description

The U022-006-COIL USB 2.0 Hi-Speed A/B Coiled Cable (M/M) connects your computer, laptop or other compatible USB-A device to a USB-B peripheral, such as printers and scanners. This 6-ft. (1.83 m) cable supports data transfer rates up to 480 Mbps for both low- and high-speed devices, including multimedia applications.

The specially coiled cable takes up much less space than a regular 6-ft. (1.83 m) cable. It also resists tangles and knots, making it convenient to store in your car or carry in your purse, backpack or laptop bag.

Molded nickel-plated connectors ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

Features

Connect Your USB Type-B Peripherals to Your Computer

- Ideal for printers and scanners
- Supports data transfer rates up to 480 Mbps
- Backward compatible with earlier USB generations

Coiled to Take Up Less Space than Regular 6-ft. (1.83 m) Cable

- Resists tangles and knots
- Stores perfectly in car, purse, backpack or laptop bag

First-Rate Construction for Superior Signal Transfer

- Molded nickel-plated connectors for optimal signal quality

Highlights

- Supports data transfer rates up to 480 Mbps
- Molded nickel-plated connectors
- Twisted 28/24 AWG data/power lines
- 6-ft. (1.83 m) cable is coiled to take up less space

System Requirements

- Any USB device requiring a USB cable
- USB 2.0 performance only when used with USB 2.0 device and USB 2.0 controller

Package Includes

- U022-006-COIL USB 2.0 Hi-Speed A/B Coiled Cable (M/M), 6-ft. (1.83 m)



- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332197276
Technology	USB 2.0 (High Speed); USB
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Shipping Dimensions (hwd / cm)	22.86 x 16.26 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 6.40 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)
STANDARDS & COMPLIANCE	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>