

Expression Premium XP-640

DATASHEET



Produce outstanding photos and crisp, clear text with this Wi-Fi, all-in-one, with individual inks, a large LCD screen and two paper trays

Produce your very own high-quality photos and text documents at home with our XP-640. You can replace just the colour you've used, as it uses individual ink cartridges. Enjoy the freedom of printing away from your desktop with Epson Connect, which offers a range of mobile printing options. It also has a colour LCD screen and a range of additional features.

Best of both worlds

Create outstanding photos and crisp, clear text documents with the five-colour Claria Premium dye and pigment ink-set. Photographs will be crystal clear with vibrant colours and deep, rich blacks thanks to the addition of a Photo Black ink cartridge. The use of individual ink cartridges means only the colour used need to be replaced to help save on ink costs.

Mobile printing


Printing photos and documents on the go is easy with the XP-640. Unlock the potential of your smartphone or tablet by downloading the iPrint app¹ to print and scan wirelessly. Make the most of your Facebook photos with the Creative Print¹ app, which allows you to print photos directly, create custom greeting cards, turn photos into colouring book templates, and plenty more. In addition, you can email documents and photos directly to the printer from almost anywhere in the world with Epson Email Print¹.

Easy to use features

For easy navigation, the XP-640 comes with a 6.8cm LCD screen and touch panel. Dual paper trays and fast, double-sided printing can help to save time and paper. Users can also slot in a memory card and follow the helpful menu prompts to print photos without a PC. It's also possible to print on suitable CDs and DVDs.

KEY FEATURES

- **Compact Wi-Fi all-in-one**
Print, scan and copy
- **Mobile printing**
Freedom to print and scan from almost anywhere¹
- **Wi-Fi and Wi-Fi Direct**
Wireless printing with or without a network
- **Dual paper trays**
One for A4 and another for photo paper
- **6.8cm LCD screen with touchpad**
Scan, copy and print photos directly from a memory card



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	1.5 pl, With Variable-Sized Droplet Technology
Ink Technology	Claria™ Premium Ink
Printing Resolution	5,760 x 1,440 dpi

PRINT

Printing Speed ISO/IEC 24734	13 Pages/min Monochrome, 10 Pages/min Colour
Maximum Printing Speed	32 Pages/min Monochrome (plain paper), 32 Pages/min Colour (plain paper), 20 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper)
Colours	Black, Photo Black, Cyan, Yellow, Magenta
For detailed information on printing speeds please visit http://www.epson.eu/testing .	

SCAN

Scanning Resolution	1,200 dpi x 2,400 dpi (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

PAPER / MEDIA HANDLING

Number of paper trays	2
Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, 9 x 13 cm, 10 x 15 cm, 13 x 18 cm, 13 x 20 cm, 20 x 25 cm, 100 x 148 mm, 16:9, Legal
Duplex	Yes
Print Margin	0 mm top, 0 mm right, 0 mm bottom, 0 mm left (Wherever margin is defined. Otherwise 3mm top, left, right, bottom.)
Paper Tray Capacity	100 Sheets Standard, 20 Photo Sheets
Media Handling	Automatic duplex, Borderless print, CD/DVD print

GENERAL

Energy Use	15 W (standalone copying, ISO/IEC 24712 pattern), 1.1 W (sleep mode), ENERGY STAR® qualified
------------	--

OTHER

Warranty	12 months Carry in Optional warranty extension available
----------	---

LOGISTICS INFORMATION

SKU	C11CF50401
EAN code	8715946614748
Multiple Order Quantity	1 Units
Country of Origin	Indonesia
Pallet Size Euro	30 Units
Pallet Size Block	44 Units

Expression Premium XP-640

WHAT'S IN THE BOX

- Individual Ink Cartridges
- Main unit
- Power cable
- Setup guide
- Software (CD)
- Warranty document

INK CARTRIDGE COMPATIBILITY



INK YIELD DATA



Oranges
33XL

Oranges 33

●	530 pages*	250 pages*
●	400 photos*	200 photos*
● ●	650 pages*	300 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pagewayield>



For more information please contact:

Telephone: 01952 607111 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740
+ Local call rate.

Web: www.epson.co.uk
www.epson.ie

1. Epson iPrint and Epson Creative Print require a wireless connection and the Epson printing apps. Epson Email print, Epson scan-to-cloud and Epson Remote print driver require an internet connection. For more information, supported languages and devices, please visit www.epsonconnect.eu

EPSON®

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.