

# JTouch Whiteboard

## with Capacitive Touch Technology

Part #: INF7002WB

The JTouch Whiteboard with Capacitive Touch makes presentations, instruction, and group work more dynamic and engaging. Foster collaboration and creativity and bring presentations to life with a brilliant 4K touchscreen display that's bright and clear in any light.

### Key Features

- Beautiful 4K image, video, and presentation content, with capacitive touch interactivity
- Built-in, full-featured digital whiteboard lets you capture and save notes electronically
- Display your PC, Mac, or Chromebook via HDMI, VGA, or component video and control it from the touchscreen
- Enable touch from your computer
- Easily accessible 4-port USB hub



Shown with optional cart  
(INA-MCARTDX)



### Projected Capacitive Touch (PCAP)

The ultra-responsive technology found in tablets and smart phones is now in your JTouch.

- Multi-point touch allows multiple people to write or draw at the same time
- No calibration required
- Works with finger, stylus, and medical grade gloves
- Sleek, bezel-less design

### Interactive Whiteboard

Draw, write, and capture notes.

- Scroll seamlessly on a multi-screen canvas, with room for free-form drawings, diagrams, and notes
- Write or draw with a complete collection of digital pens, highlighters, shapes, and lines from a continuous spectrum colour wheel
- Paste backgrounds and images onto a whiteboard or wallpaper the entire canvas
- Multiple colours, shapes, and backgrounds are available to help you communicate your ideas



## Specifications\*

INF7002WB

Size	70" diagonal
Resolution	4K (3840 x 2160 pixels)
Anti-Glare Option Available	No
Mounting Orientation	Landscape
Refresh Rate	120 Hz
Viewing Angle	176°
Technology	Direct LED backlight
Pixel Pitch	0.40mm x 0.40mm
Response Time	6 ms
Contrast Ratio	5000:1
Brightness	350 cd/m <sup>2</sup>
Input Connections	DisplayPort 1.2, HDMI 2.0 x 2, HDMI 1.4, VGA, component, 3.5mm audio in, RCA stereo in, RS232, USB-B for touch screen control
Output Connections	RCA stereo audio out, 3.5mm stereo out
Touch Screen	10-point, projected capacitive
Speakers (Integrated)	10W x 2
Mount	VESA standard 400 x 400 mm, M6 screws
Accessories Included	Stylus, VGA cable, USB cable, power cord, remote, quick setup guide
Product Weight	49kg
Product Dimensions (H x W x D)	1629.8 x 106.6 x 963.3 mm
Shipping Weight	62 kg
Shipping Dims (H x W x D)	1860 x 260 x 1180 mm

## On-Board System

Input	2 USB, 1 RJ45
Built-in Tool	Whiteboard
CPU	Arm Cortex-A9 Quad-Core
GPU	Mali-450 Octo-Core
RAM	2GB DDR3
Flash Memory	8GB

## Optional Accessories

- Wall Mount for 50-70 Inch Display (INF-WALLMNT2)
- Deluxe Mobile Cart with PTZ Mount and Accessory Shelf (INA-MCARTDX)
- Lift Assist Mount for 57-70 Inch Display (INA-MNTBB70)
- Floor Support for Lift Assist Wall Mount (INA-SUPPORTBB)
- Mobile Cart for List Assist Mount (INA-CARTBB)
- VESA Interface Bracket (INA-VESABB)
- Touchscreen Stylus (INA-STYLUS)
- Extended Warranties (EPWHW70JT1)
- LiteShow4 (INLITESHOW4)

## Display Specifications

- Refresh Rate: 120 Hz
- Viewing Angle: 176°
- Computer Touch Compatibility (via USB): PC, Mac, Chromebook
- Power: AC 100 to 240V, 50/60 Hz
- Operating Conditions: 0° to 40° at 0 to 3,048 m
- Noise: <40dBA at 25° C
- Warranty: 2 Year



LiteShow 4 Wireless  
presentation adapter  
INLITESHOW4

\*Product specifications, terms, and offerings are subject to change at any time without notice.