

The feature-rich Planar® PXN2770MW 27" Full HD LCD monitor features thin borders, wide viewing angles, HDMI, DisplayPort and Analog (VGA) video inputs and speakers. With a narrow bezel, the Planar PXN2770MW is perfect for mounting on a multi-monitor stand in space-constrained office environments.



SPECIFICATION	DETAIL
<b>Product Name</b>	PXN2770MW
<b>Planar Part Number</b>	997-8369-00
<b>Viewable Size</b>	27" diagonal (23.54" horizontal x 13.24" vertical)
<b>Aspect Ratio</b>	16:9
<b>Contrast Ratio (typ)</b>	1000:1
<b>Viewing Angle (typ)</b>	178° Horizontal and 178° Vertical (Specified at CR>10:1)
<b>Response Time (typ)</b>	14 ms
<b>Brightness (Typical)</b>	250 cd/m <sup>2</sup>
<b>Display Type</b>	IPS LCD Active Matrix Flat Panel Display (TFT)
<b>Display Resolution</b>	1920 x 1080, full HD
<b>Tilt Range</b>	-5° to +20°
<b>Palette</b>	16.7 million colors
<b>Pixel Pitch</b>	0.3114 mm
<b>Refresh Rate</b>	55-76Hz (60Hz recommended)
<b>Dimensions (W x H x D)</b>	24.4" x 17.4" X 9.8" (620.2 mm x 442.6 mm x 248.5 mm)
<b>Dimensions without Stand</b>	24.4" x 14.3" x 1.8" (620.2 mm x 362.2 mm x 45.1 mm)
<b>Panel Depth</b>	1.8" (45.1 mm)
<b>Display Weight</b>	11.3 lb (5.1 kg) , 10.8 lb (4.9 kg) without base & stand
<b>Shipping weight</b>	14.4 lb (6.5 kg)
<b>Video Inputs</b>	HDMI, DisplayPort, VGA
<b>HDCP</b>	Yes

<b>Audio Output</b>	2W x 2, headphone out
<b>External Connections</b>	HDMI 19-pin, DisplayPort 20-pin, VGA 15-pin, 3.5 mm audio in, 3.5mm headphone out
<b>Compatibility</b>	PC and Mac® (adapter may be required for Mac)
<b>Power Supply</b>	Internal
<b>Power Consumption (max)</b>	32 Watt Typical (<0.5 Watt standby)
<b>Power Requirements</b>	AC 100/240 VAC
<b>VESA Compatible/Location</b>	Built-in 100 mm VESA, back
<b>Product Approvals</b>	UL, FCC-B, CE, cUL, RoHS
<b>Recommended Usage</b>	Up to 16 hours per day
<b>Service and Support</b>	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only). Please see warranty document for more details and for replacement procedures outside the US.
<b>Options / Features</b>	Wide color consistent viewing angle, nearly borderless bezel, discreet branding, anti-glare coating, multi-language display, on screen display (OSD), Kensington® Security Slot
<b>In the Box</b>	PXN2770MW 27" LED LCD Monitor, Power Cord, VGA Cable, DisplayPort Cable, Audio Cable, User's Guide
<b>UPC</b>	8 10689 00316 8

For more information, please visit [www.planar.com](http://www.planar.com)

*Specifications are subject to change without notice.*

*Specification Report Date: 11/3/2016*

*© Copyright 2016 Planar Systems, Inc. All rights reserved*