



AOC Monitors
Curved Monitor

83 Series
35", 2560 x 1080 @144Hz

C3583FQ

35-inch Curved Display for Immersive Media Experience

AOC's new curved display is here. The C3583FQ features a cinematic 35-inch VA curved panel. This provides the best viewing angles that allows users to see more in an immersive viewing experience.

Key Features

- 35" curved VA panel with 2560 x 1080 Full HD Resolution
- Fast 144Hz refresh rate via DP/Adaptive Sync
- VGA, DVI, MHL-HDMI (2x), Display Port (2x) connectivity
- Two 5-watt speakers and Audio Line-in/out
- Narrow bezels for multi-monitor setup
- 300 Nits of Brightness
- 4ms Response Time

AOC

C3583FQ

Curved Full HD Resolution

AOC's C3583FQ features a curved panel with detailed 2560 x 1080 resolution and fast 144Hz refresh rate via DP/Adaptive Sync. The VA panel has wide-viewing angles, allowing users to enjoy consistent color uniformity and accuracy at all angles. The C3583FQ has 50,000,000:1 dynamic contrast ratio with 4ms response time.



Immersive Visual Experience

Human eyes are not flat and perceive the world around us in angles and curves. Curved monitors deliver the best viewable angles that allow users to see more. Aside from the appeal of an immersive gaming or work environment, there's a benefit in reduced eyestrain from a consistent radius between your eye and the



Rich in Connectivity

C3583FQ features VGA, DVI, two MHL-HDMI, and two Display Ports connectivity, with two 5-watt speakers and audio line-in/out for audio needs. MHL connection allows users to connect their smart device on to the bigger 35" screen while charging their devices simultaneously.



Multi-Monitor Curved Setup

Curved displays allow for an impressive multi-monitor setup as borders flow and blend into each other. Users will be able to experience peripheral vision realism in first person shooters or racing games, just like if you were there in real life.

C3583FQ Specification

Cabinet Color	Glossy black with aluminum hair line stand
Panel	TFT Active Matrix, LED Backlight, VA curved panel (2000R) 35" Class Widescreen, 21:9 Aspect Ratio 35" Viewable Image Size, Diagonal
Pixel Pitch	0.32 (H) mm x 0.32 (V) mm
Display Area	819.84 mm(H) x 345.87 mm(V)
Brightness	300 cd/m ² (typ)
Contrast Ratio	50,000,000:1 (dynamic)
Response Time	4ms
Viewing Angle	Horizontal: 178 Degrees (CR>10) Vertical: 178 Degrees (CR>10)
Scanning Frequency	Horizontal: 30K~99KHz Vertical: 50~76 Hz
Optimal Resolution	2560x1080@160Hz (DP/Adaptive Sync)* 2560x1080@144Hz (DP/Adaptive Sync) 2560x1080@60Hz (VGA, DVI, HDMI)
Recommended	2560x1080@144Hz
Supported Resolutions	640x480@60/67/72/75Hz, 720x400@70Hz, 800x600@56/60/72/75Hz, 832x642@75Hz, 1024x768@60/70/72/75Hz, 1280x720@60Hz, 1280x1024@75Hz, 1280x960@60Hz, 1440x900@60Hz, 1680x1050@60Hz, 1920x1080@60Hz
Color Depth	16.7 Million colors
Connectors	1 x VGA, 1 x DVI, 2 x MHL-HDMI 1.4, 2 x Display Port 1.2
Audio	5-watt speakers (2x), Audio line-in/out
User Control	Source/Auto/Exit, Clear Vision, Volume, Menu/Enter, Power
Adjustability	Tilt: -3.5°±1.5°~+21.5±1.5°
Power Source	Universal 110~240VAC, 50/60Hz
Power Consumption	Power On: 60W (Typical), Standby: <0.5W
Regulations	cTUVus, CE, FCC, RoHS, Windows 8/10 compatible
Other Features	Curved VA panel, extra narrow bezel, Kensington Security Slot, User Friendly Graphical OSD Menu, AOC's eSaver Software, i-Menu Software
Dimensions (WxHxD mm)	Monitor: 844.6 x 458 x 213.6, Carton: 980 x 280 x 610
Dimensions (WxHxD inches)	Monitor: 33.25 x 18.03 x 8.4, Carton: 38.6 x 11 x 24
Weight (Net)	25.57 lbs (11.6 kgs) Net
Weight (Gross)	34.16 lbs (15.5 kgs) Gross
Loading Qty w/pallet	20' = 120 pcs.; 40' Std = 288 pcs.
UPC Code	685417712687
What's in the Box	35" Curved Monitor, Power Cord, Power Adapter, HDMI cable, DP cable, Audio cable, Quick Start Guide

Disclaimer *2560x1080@160Hz (OD) – Your specific hardware may support 160Hz but AOC provides no guarantee of availability or performance.

1. Wall mount arm & bracket not included. Actual product may vary from image shown on datasheet. The information contained herein is subject to change without notice. AOC shall not be liable for technical or editorial errors or omissions contained herein. All other trademarks are property of their respective owners. For more information, visit us.aoc.com or call 888-838-6388