



Overview

Model Name	APC Smart-UPS 750VA LCD RM 120V with Network Card
Includes	CD with software , Documentation CD , Installation guide , Rack Mounting support rails , Smart UPS signalling RS-232 cable , Temperature Probe , USB cable
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Output

Output Power Capacity	500 Watts / 750 VA
Max Configurable Power (Watts)	500 Watts / 750 VA
Nominal Output Voltage	120V
Nominal Output Voltage	Line Interactive
Waveform Type	Sine wave
Output Connections	(6) NEMA 5-15R (Battery Backup)

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA L5-15P
Cord Length	8 feet (2.44 meters) (2.44 meters)
Input voltage range for main operations	82 - 144 V
Input voltage adjustable range for mains operation	75 - 154V
Maximum Input Current	0 A
Input Breaker Capacity	0 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 hour(s)

Replacement Battery	APCRBC123
RBC Quantity	1

Communications & Management

Interface Port(s)	RJ-45 10/100 Base-T , RJ-45 Serial , SmartSlot , USB
Available SmartSlot™ Interface Quantity	0
Pre-Installed SmartSlot™ Cards	AP9631
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators , Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional

Surge Protection and Filtering

Surge energy rating	459 joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	3.5 inches (89.0 mm) (89.0 mm)
Maximum Width	17.0 inches (432.0 mm)
Maximum Depth	16.0 inches (406.0 mm) (406.0 mm)
Rack Height	2 U
Net Weight	38.0 lbs (17.24 kg) (17.24 kg)
Shipping Weight	46.7 lbs (21.18 kg) (21.18 kg)
Shipping Height	9.5 inches (241.0 mm) (241.0 mm)
Shipping Width	21.5 inches (546.0 mm) (546.0 mm)
Shipping Depth	23.0 inches (584.0 mm) (584.0 mm)
Master Carton Units	0.0
Master Carton Weight	0.0 lbs
Color	Black
Units per Pallet	16.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C) (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters) (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C) (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters) (0-15000 meters)
Audible noise at 1 meter from surface of unit	42.000 dB
Online Thermal Dissipation	46.000 BTU/hr

Conformance

Approvals	CSA , FCC Part 15 Class A , UL 1778
Standard warranty	3 years repair or replace (excluding battery) and 2 years for battery
Equipment protection policy	Lifetime : \$150000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs

Battery Directive	Compliant
Battery Notes	Battery Notes
