

H4 Series 50-inch Class Hisense • Roku TV Specifications

Model Name	50H4C
Series Name	H4
Package Details	
Product Dimension (Without the stand)	44.3"W x 25.6"H x 9.72" D inches
(With the stand)	44.3"W x 27.7"H x 9.72"D inches
Weight (Without the stand)	27.6 pounds
(With the stand)	28.2 pounds
DISPLAY	
Active screen size (diagonal)	49.5 inches
Screen type	Flat
Type of TV	
Smart TV	Yes, Roku platform
PICTURE QUALITY	
Screen resolution	1920 x 1080p
Local Dimming	No
Local Dimming Zones	No
4K Upscaling	No
Ultra Smooth Motion	Yes
AUDIO	
Audio output power (Watts)	10W x 10W
Audio technologies	Supports Dolby Digital
LANGUAGES	
On-Screen Display	English, Spanish and French
POWER	
Power Consumption	120W (max)
Standby Consumption	<1W
Power Supply	AC 120V, 60Hz
CONNECTIVITY	
Wireless Built-in	Yes (2x2 Dual-Band 802.11ac)
Ethernet	No
AirBridge® (Hisense-developed technology for content sharing between devices)	Yes (CAST)
HiMedia® (Hisense-developed technology for playing digital content stored on a USB device or in the Cloud)	Yes (DLNA)

PORTS	
HDMI	3
Ethernet (LAN)	1
USB	1
RF Antenna	1
RCA Composite Video Input	1 (shared with component)
L/R Audio Input for Composite	1 (shared with component)
RCA Component Video Input	0
L/R Audio Input for Component	0
Digital Audio Output	1 Optical
Earphone/Audio Output	1
Channels & Apps	
Streaming channels	Over 3000+ channels
Apps	Netflix, Amazon Instant Video, Vudu, YouTube, Pandora, App Store
CERTIFICATIONS	
Performance and Compliance Certifications	HDMI™, VESA®, Dolby® Digital Plus, FCC®, UL®
OTHER FEATURES	
4K UHD Upscaling	No
Noise Reduction	Yes
Universal Control Capability for remote	No
Web Browser	No
Parental Control	Yes
Closed Caption	Yes
Sleep Timer	Yes
Wall Mountable	Yes, VESA 200x400
Warranty	2-year warranty available
UPC Code	888143001685