

Color
imageCLASS
LBP712Cdn

Color, Duplex, Laser Printer



LBP712Cdn Tags:

Short Tag

Medium Tag

Long Tag

Lightning-fast, mobile ready printer delivers exceptional color laser output.

Lightning-fast, AirPrint printer delivers exceptional color laser output, generous, expandable paper capacity and a variety of mobile solutions for printing on the go.

Lightning-fast, AirPrint printer with easy to use, tiltable display delivers exceptional color and monochrome laser output at 40 pages per minute, generous, expandable paper capacity and various mobile solutions for printing on the go.



Features:

- Print up to 40 pages per minute in both color and black and white (letter sized)
- Print on the go with Canon PRINT Business, Apple® AirPrint®, Mopria™ Print Service, Google Cloud Print™
- PCL and Adobe® PostScript® support
- Achieve high-quality printing and sharp, vibrant colors using V² (Vivid and Vibrant) Color Technology
- USB Direct Print allows you to print from your USB flash drive in JPEG, TIFF, XPS and PDF formats
- Energy saver mode uses 2.2 watts or less in USB sleep mode
- 550-sheet capacity cassette, 100-sheet multipurpose tray and optional 550-sheet cassette (up to 3) give you a total 2,300 max paper capacity
- User-friendly 5 line LCD panel for easy navigation
- Print securely with SNMPv3, IP / MAC address filtering, HTTPS/IPPS, IEEE802.1x (wired LAN)

- Functions
- Replaces
- Print Speed
- Duplex
- First Print Out Time
- Print Resolution
- Print Memory
- Print Features
- Printer Language
- Network Security
- Connectivity
- Operating Systems
- Paper Capacity (Standard)
- Paper Capacity (Optional)
- Min / Max Paper Size
- USB Direct Print
- Display Panel
- Duty Cycle
- Energy Consumption
- Energy Star
- EPEAT

Product Specifications	
	LBP712Cdn
	Print
	LBP7780Cdn
	Up to 40 ppm (letter size)
	Yes
	6 seconds or less (letter size)
	Up to 600 x 600 dpi, 9600 equivalent x 600 dpi
	1 GB
	Watermark, Page Composer, Toner Saver, Poster, Booklet, Collate
	UFR II, PCL5c/e, PCL6 and Adobe® PostScript®
	SNMPv3, IP / MAC address filtering, HTTPS/IPPS, IEEE802.1x (wired LAN)
	USB Device 2.0 High-Speed, 10/100/1000 Base-T Ethernet (Network)
	Windows® 10/8.1/8/7, Windows Vista®, Windows Server® 2012 R2/2012/2008 R2/2008/2003 R2/2003, Mac OS 10.6.8 or later
	550-sheet capacity cassette, 100-sheet multipurpose tray
	550-sheet capacity cassette x 3 (total standard + max = 2,300 sheets)
	4 x 5.8 inches to 8.5 x 11.7 inches (standard cassette), 3 x 5 inches to 8.5 x 14 inches (multipurpose tray), 4 x 5.8 inches to 8.5 x 14 inches (optional cassette)
	Yes (JPEG, TIFF, XPS and PDF)
	5 line B/W LCD
	Up to 80,000 pages per month (recommended monthly print volume: 1,000-7,000 pages)
	Approx: 600 W (during operation), 33 W (standby), 2.2 W (USB, energy saver / sleep mode), 1.2 W (wired, energy saver / sleep mode)
	Yes
	Silver

Ordering Information

Model No.	Description	MSRP Price	Item No.	UPC Code	Box Dimensions	Box Weight	Unit Dimensions	Unit Weight w/o crq & w/crq
Color imageCLASS LBP712Cdn	Color, Duplex, Laser Printer	\$1,795	0656C002	013803266757	23.8" (W) x 23.8" (D) x 21.1" (H)	77.2 lbs.	18.1" (W) x 18.3" (D) x 15.3" (H)	54.7 / 62.7 lbs.

Accessories	Description	MAP Price	Item No.	UPC Code	Box Dimensions	Box Weight	Unit Dimensions	Unit Weight
Cartridge 040 Black	Full Yield Cartridge; 6,300 sheets ISO/IEC	\$151	0460C001	013803270044	5.8" (W) x 15.6" (D) x 6.4" (H)	2.9 lbs.	NA	2 lbs.
Cartridge 040 Cyan	Full Yield Cartridge; 5,400 sheets ISO/IEC	\$189	0458C001	013803270037				2 lbs.
Cartridge 040 Magenta	Full Yield Cartridge; 5,400 sheets ISO/IEC	\$189	0456C001	013803270020				2 lbs.
Cartridge 040 Yellow	Full Yield Cartridge; 5,400 sheets ISO/IEC	\$189	0454C001	013803270013				2 lbs.
Cartridge 040 Black Hi-Capacity	Hi-Capacity Cartridge; 12,500 sheets ISO/IEC	\$211	0461C001	013803270082		3.1 lbs.		2.2 lbs.
Cartridge 040 Cyan Hi-Capacity	Hi-Capacity Cartridge; 10,000 sheets ISO/IEC	\$292	0459C001	013803270075				2.2 lbs.
Cartridge 040 Magenta Hi-Capacity	Hi-Capacity Cartridge; 10,000 sheets ISO/IEC	\$292	0457C001	013803270068				2.2 lbs.
Cartridge 040 Yellow Hi-Capacity	Hi-Capacity Cartridge; 10,000 sheets ISO/IEC	\$292	0455C001	013803270051				2.2 lbs.
Paper Feeder PF-D1	550-sheet cassette	\$325	0942C001	013803265729	9.8" (W) x 23.2" (D) x 23.2" (H)	17.7 lbs	18.1" W x 18.3" D x 5.2" H	13.5 lbs.
Waste Toner WT-B1	Waste Toner Box	\$95	0942C002	013803266740	3.8" (W) x 18.8" (D) x 7" H	4.6 lbs		
Optional Cabinet Stand		TBD						

eCarePAK	Description	MSRP Price	Item No.
Tier 20 1-Year	1-Year Limited Onsite	\$160	5707B058
Tier 20 2-Year	2-Year Limited Onsite	\$215	5707B059
Tier 20 3-Year	3-Year Limited Onsite	\$315	5707B060
Tier 20 4-Year	4-Year Limited Onsite	\$490	5707B061

Other Information
Country of Origin: China
Harmonized Codes: 8443310000

What Comes in the Box
LBP712Cdn Product
Standard Cartridge 040 CMYK
Power Cord
Starter Guide
User Software DVD-ROM
Canon Drivers
Warranty Card

Shipping Information

# Boxes per Pallet	4
Hi / Ti	1/4
Pallet Dimensions (Pallet + Box)	47.8" (W) x 47.8" (D) x 26.4" (H)
Dimensions w/out Pallet	47.6" (W) x 47.6" (D) x 21.1" (H)
Pallet Weight (Pallet + Box)	353 lbs.