


24-Port 1U Rack-Mount STP Shielded Cat5e/6 Feedthrough Patch Panel with 90-Degree Down-Angle Ports, RJ45 Ethernet, TAA

MODEL NUMBER: N254-024-SH-D



Manages and organizes Cat5e/6 input and output cable connections in your high-density Ethernet network. RJ45 ports face downward to ease cable installation. Ideal for MDFs and IDF's where quick patching changes are necessary.

Description

The N254-024-SH-D 24-Port 1U Rack-Mount STP Shielded Cat5e/6 Feedthrough Patch Panel features RJ45 ports that point downward at a 90-degree angle to ease cable installation in hard-to-reach places. It meets or exceeds Cat6 specifications and works with USOC, T568A and T568B wiring to comply with industry standards. It's ideal for MDFs (main distribution frames) and IDF's (intermediate distribution frames) where quick patching changes are necessary.

Made from heavy-duty 14ga cold-rolled steel, the N254-024-SH-D manages and organizes the cabling in your high-density network with no 110 punchdown termination required. Just plug your Cat5e/6 cables into the 24 fully shielded RJ45 coupler jacks on both sides of the panel. Ports are clearly numbered to help you identify connections.

Mounts easily into 1U of an EIA-standard 19-inch rack. Grounding wire included. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

STP Cat6 Patch Cord

Features

Manages and Organizes High-Density Network Cabling

- Meets or exceeds Cat6 specifications
- Heavy-duty 14ga cold-rolled steel construction
- Works with USOC, T568A and T568B wiring to comply with industry standards
- Ideal for MDFs and IDF's where quick patching changes are needed

24 Fully Shielded RJ45 Coupler Jacks

- 90-degree down-angle installation for easy cable connection in hard-to-reach places

Highlights

- No 110 punchdown termination required
- Works with USOC, T568A and T568B wiring
- Heavy-duty 14ga cold-rolled steel construction
- Numbered ports for easy connection identification
- Mounts into 1U of EIA-standard 19 in. rack

Package Includes

- N254-024-SH-D 24-Port 1U Rack-Mount STP Shielded Cat5e/6 Feedthrough Patch Panel
- (24) Cat6 Shielded Snap-In Couplers (RJ45 F/F)
- Grounding wire
- Mounting hardware
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Ports are clearly numbered for easy identification
- Low-profile form factor requires no 110 punchdown termination

Quick, Easy Installation

- Mounts easily into 1U of EIA-standard 19 in. rack
- Includes grounding wire

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

Specifications

OVERVIEW	
UPC Code	037332197481
Technology	Cat5/5e; Cat6
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	7.11 x 6.86 x 49.78
Shipping Dimensions (hwd / in.)	2.80 x 2.70 x 19.60
Shipping Weight (kg)	1.00
Shipping Weight (lbs.)	2.20
CONNECTIONS	
Ports	24
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Warranty Details	LIFETIME LIMITED WARRANTY

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>