

MFC-J5330DW

Print • Copy • Scan • Fax

BUSINESS SMART PLUS SERIES



Color Inkjet All-in-One for Small Business

Built for Business Performance

- Spend less time waiting on printouts for when you need your documents fast.

Flexible Paper Handling

- 250-sheet paper tray capacity accepts up to 11"x17". Single sheet bypass tray for printing on envelopes and card stock for added convenience.

2.7" Touchscreen Display

- Easily navigate to powerful features with a 2.7" Touchscreen display.

Help Increase Productivity

- Up to 50-sheet ADF¹ and automatic duplex (2-sided) printing.

Great Ink Produces Great Results

- Sharp black text and high impact color documents on plain paper.

Super High-yield Ink Cartridges

- Genuine Brother replacement ink cartridges offer additional page yields while helping to lower printing costs².

Print and Scan From Almost Anywhere³

- Smartphone, tablet, laptop, and desktop computer.

Break Free and Go Wireless

- Enjoy the freedom of wireless connectivity⁴ - and no router needed with Wi-Fi Direct®.

Scan to Popular Cloud Services

- Directly from the machine: including Google Drive™, Dropbox, Evernote, and more⁵. Capture and digitize paper documents with Brother Cloud Apps for electronic storage or sharing⁶.

Warranty & Support

- Two-year limited warranty and free phone support for the life of the product



1 Up to 30-sheet sort copy

2 Based on MSRP of individual LC3019 black and color ink cartridges and approximate page yield in accordance with ISO/IEC 24711. Additional purchase required. For more page yield information, see www.brother.com/pageyield.

3 Requires connection to a wireless network. See www.connectprintshare.com for details, availability and mobile device compatibility.

4 Requires connection to a wireless network. For more details visit www.connectprintshare.com.

5 Requires internet connection and an account with desired service. For more details see www.connectprintshare.com.

6 Requires internet connection. For more details visit www.connectprintshare.com.

Specifications:

| | |
|---|---|
| Print Technology | 4-cartridge Color Inkjet |
| LCD Display | 2.7" Color TouchScreen Display |
| Paper Size (maximum) | Paper Tray: Up to 11" x 17" (ledger size) Bypass Tray: Up to 11" x 17" (ledger size) |
| Print Speed (maximum)* | Black (ISO/IEC 24734): Up to 22ppm Color (ISO/IEC 24734): Up to 20ppm |
| FPOT (First Print Out Time) | Black: Approx. 5.5 Seconds Color: Approx. 6.0 Seconds |
| Print Resolution (maximum)† | Up to 4800 x 1200 dpi |
| Duplex Printing Capability | Yes (up to 8.5"x11") |
| Borderless Printing Capability‡ | Yes (Letter, A4, Ledger, A3) |
| Paper Input Capacity (maximum) | Up to 250 sheets plus single sheet bypass tray |
| Auto Document Feeder‡ | Yes (up to 50-sheets) |
| Standard Interfaces* | Wireless (802.11 b/g/n), Ethernet, Wi-Fi Direct®, Hi-speed USB 2.0 |
| Copy Speed (maximum)* | Black (ISO/IEC 24735): 12 Color (ISO/IEC 24735): 9 |
| Copy Resolution (maximum)† | Up to 4800 x 1200 dpi |
| Copy Reduction / Enlargement | 25% - 400% in 1% increments |
| Copy Options | Stack, Sort, N-in-1, ID Copy, Remove Background Color |
| Duplex Scan and Copy | No |
| Scanner Type | Color Flatbed (CIS) |
| Document Glass Size | Letter (8.5" x 11.7") |
| Scan / Copy Size (maximum) | Letter (8.5" x 11") |
| Scan Resolution (maximum)† | Optical: 2400 x 1200 dpi (Flatbed) Interpolated: 19200 x 19200 dpi |
| Scan To Capabilities | ID Scan, Image, OCR, Email, File, USB Memory, FTP‡, Email Server (download), Network |
| Fax Modem | 14.4 Kbps |
| Fax Page Memory (maximum)ˆ | Up to 200 pages |
| Speed Dial Locations | 100 x 2 |
| PC Fax Capability¹ | Yes (black & white only) |
| Web Connectivity² | FACEBOOK™, FLICKR®, GOOGLE DRIVE™, EVER- NOTE®, DROPBOX, BOX, ONEDRIVE®, ONENOTE®, BROTHER CLOUD APPS, SharePoint Online |
| Brother Cloud Apps³ | Scan to Office, Office Print, Easy Scan to Email, Scan to Mobile, Scan to Searchable PDF, Outline&Copy, Outline&Scan, NoteScan, CreativeCenter, Fax Forward to Cloud / Email |
| Near Field Communication (NFC) | No |
| Operating Systems Compatibility⁴ | PC: Windows 10, 8.1, 8, 7, Vista; Windows Server 2012, 2012 R2, 2008, 2008 R2; MAC: OS X v 10.11.x, 10.10.x, 10.9.5.x |
| Mobile Device Compatibility⁵ | AirPrint®, Google Cloud Print™, Brother iPrint&Scan, Wi-Fi Direct®, Mopria |
| Maximum Monthly Duty Cycle⁶ | Up to 30,000 pages |
| Recommended Monthly Volume⁷ | Up to 2,000 pages |
| Warranty | 2-Year Limited Warranty |
| ENERGY STAR Qualified | Yes |

Supplies & Accessories†:

| | |
|-----------|--|
| LC3019BK | Super High Yield Black Ink Cartridge (approx. 3000 pages)* |
| LC3019C | Super High Yield Cyan Ink Cartridge (approx. 1500 pages)* |
| LC3019M | Super High Yield Magenta Ink Cartridge (approx. 1500 pages)* |
| LC3019Y | Super High Yield Yellow Ink Cartridge (approx. 1500 pages)* |
| BP71GLTR | Letter-size Glossy Inkjet Paper (20 sheets)* |
| BP71GLGR | Ledger-size Glossy Inkjet Paper (20 sheets)* |
| BP71GP20 | 4" x 6" glossy paper* |
| BP71GP20 | Letter-size Multi-Purpose Paper (500 sheets)* |
| BP60MPLTR | Letter-size Multi-Purpose Paper (500 sheets)* |

Carton Contents:

| |
|--|
| Brother MFC-J5330DW |
| LC3017BK/C/M/Y Black, Cyan, Magenta, Yellow High Yield Ink Cartridges‡ |
| Product Safety, Quick Setup and Basic User's Guides |
| Installation CD-ROM for Windows® and Mac OS‡ |
| Telephone Line Cord |

Setup Information:

| | |
|---------------------------------|-----------------------------|
| UPC Code | 012502645047 |
| Unit Dimensions | 20.9" W x 15.7" D x 12.0" H |
| Unit Weight | 36.8 lbs |
| Carton Dimensions | 25.1" W x 18.4" D x 17.2" H |
| Carton Weight | 44.1 lbs |
| Pallet Quantity | 6 |
| Pallet Tiers | 2 |
| Pallet Quantity per Tier | 3 |
| Pallet Size | 48" x 40" |
| Pallet + Cartons Height | 39.4" |
| Pallet + Carton Weight | 294.6 lbs |
| Country of Origin | China |
| Tariff / Harmonized Code | 8443.31.0000 |

Scannable Barcode:



012502645047

* PPM is based on printing in FAST mode and excludes time to complete first page and will vary depending on a variety of factors. ISO print speed is based on ISO/IEC 24734. ISO copy speed is based on ISO/IEC 24735. See www.brother.com/printspeed for details.

† Resolutions are listed vertical by horizontal dpi.

‡ Borderless not available on duplex. Minimum default margins 0.12" on all sides.

ˆ Cables not included.

¹ Black and white only. Based on ITU-test Chart No.1 at standard resolution with MMR compression.

² Additional purchase required.

³ Actual yield of starter cartridge will be approx. 80% of replacement LC3029 Black, and 65% of replacement LC3029 Color Series, due to ink system initialization. Approximate page yield in accordance with ISO/IEC 24711. For more page yield information, see www.brother.com/pageyield.

⁴ Up to 30-sheet sort copy

⁵ Over SSL supported.

¹ PC-Fax Send only for Mac® users.

² Requires internet connection and an account with a desired service. See www.brother.com for details.

³ Requires internet connection. See www.brother.com for details.

⁴ See system requirements on www.brother.com

⁵ Requires connection to a wireless network. See www.brother.com for details, availability, and mobile device compatibility.

⁶ Maximum number of printed pages per month and can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

⁷ The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond the range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.