



EAN Code	4026631059886
Order number	HSM2361
Shredder material	
Cutting type	Strip cut
Security level (DIN 66399)	<b>P-2 O-2 T-2 E-2</b>
Security level (DIN 32757-1)	2
Cutting width	1/4 in
Intake width	11.8 in
Container volume	34.3 gal

Cutting capacity (70g/m <sup>2</sup> )	40-42 sheets
Power consumption of the motor	590 W
Voltage	115 V
Frequency	60 Hz
Height	35 in
Width	24.4 in
Depth	19 in
Weight	105 lb
Colour	White

Technical and design modifications reserved.

Solid and reliable document shredder for small workgroups. The powerful motor with overload protection shreds documents, loyalty cards and credit cards in continuous operation safely and reliably.

- High quality materials and "Made in Germany" quality for security and durability.
- Cutting rollers made of hardened solid steel with lifetime warranty.
- Powerful motor allows for continuous operation.
- Quiet operation minimizes noise development in the workplace.
- Low power consumption in standby mode.
- Paper feed with overload protection reduces paper jams.
- The device automatically switches off if pressure is applied to the safety element.
- Light barrier for automatic start/stop.
- Mobile on castors.
- High quality wooden cabinet with door.