



Order number	HSM2363	Container volume	34.3 gal
EAN Code	4026631054096	Cutting capacity	25 - 27 sheets
Shredder material		Voltage	115 V
Cutting type	Cross cut	Frequency	60 Hz
Security level (DIN 66399)	<b>P-4 O-3 T-4 E-3 F-1</b>	Height	35 in
Security level (DIN 32757-1)	3	Width	24.4 in
Cutting width	3/16 in	Depth	19 in
Particle length	1 1/8 in	Weight	119 lb
Intake width	11.8 in	Colour	white
Power consumption of the motor	590 W	Cutting speed	17 mm/s

Technical and design modifications reserved.

Solid and reliable document shredder for small workgroups. The powerful motor with overload protection shreds documents, loyalty cards and credit cards in continuous operation safely and reliably.

- High quality materials and "Made in Germany" quality for security and durability.
- Cutting rollers made of hardened solid steel with lifetime warranty.
- Powerful motor allows for continuous operation.
- Quiet operation minimizes noise development in the workplace.
- Low power consumption in standby mode.
- Paper feed with overload protection reduces paper jams.
- The device automatically switches off if pressure is applied to the safety element.
- Light barrier for automatic start/stop.
- Mobile on castors.