

# QTH8053B

<b>Camera Type</b>	Bullet
<b>Camera Technology</b>	BNC HD
<b>Image Sensor Size</b>	1/3"
<b>Image Sensor Type</b>	CMOS
<b>Image Resolution</b>	1080P High Definition
<b>Megapixels (digital)</b>	2
<b>Effective Pixels</b>	1920x1080
<b>Lens Size</b>	3.6mm
<b>Angle of View</b>	70°
<b>IR Cut Filter</b>	Yes



Use with  
QTH Series  
BNC HD DVRs

## NIGHT VISION

IR LEDs	36
Infrared Wavelength	850nm
Min Lux Illumination	.01Lux (Color) / 0Lux with IR on (B&W)
Night Vision Range	Up to 100 ft

## ADDITIONAL IMAGE FEATURES

Auto Iris	No
On Screen Display	No
Backlight Compensation	No
Electronic Shutter	1/30-1/10,000s
Gain Control	Auto
Wide Dynamic Range	No
Noise Reduction	No

## REMOTE MONITORING

Use as Standalone	No
Compatible Mobile Devices	None, depends on DVR connected to
Compatible Systems	QTH Series BNC HD DVRs

## PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP66
Body Construction	Metal
Mounting Hardware	Screws
Weight	14 oz
Dimensions	6.4"l x 2.7"w x 3.36"h
Operating Temperature	14° to 120° F

## PTZ

Horizontal Rotation	Not applicable
Vertical Tilt	Not applicable
Preset and Cruise Patterns	Not applicable

## AUDIO

Audio Range	Not applicable
Audio Microphone	Not applicable

## CONNECTIVITY

Connector Types	BNC
Other Connections	2.1mm power
Wireless	No

## POWER

Power Supply	12V 500mA
Power Consumption	<10W (LEDs ON)