

QTH8056D

Camera Type	Dome
Camera Technology	BNC HD
Image Sensor Size	1/3"
Image Sensor Type	CMOS
Image Resolution	1080P High Definition
Megapixels (digital)	2
Effective Pixels	1920x1080
Lens Size	3.6mm
Angle of View	70°
IR Cut Filter	Yes

Use with 1080p
QTH Series
BNC HD DVRs



NIGHT VISION

IR LEDs	30
Infrared Wavelength	850nm
Min Lux Illumination	.01Lux (Color) / 0Lux with IR on (B&W)
Night Vision Range	Up to 100 ft

ADDITIONAL IMAGE FEATURES

Auto Iris	No
On Screen Display	No
Backlight Compensation	No
Electronic Shutter	1/30-1/10,000s
Gain Control	Auto
Wide Dynamic Range	No
Noise Reduction	No

REMOTE MONITORING

Use as Standalone	No
Compatible Mobile Devices	None, depends on DVR connected to
Compatible Systems	QTH Series BNC HD DVRs excluding QTH4, 8, 16

PHYSICAL ATTRIBUTES

Weatherproof	Yes
IP Rating	IP66
Body Construction	Metal
Mounting Hardware	Screws
Weight	17 oz
Dimensions	4.125"l x 3.875"w x 3.25" h
Operating Temperature	14° to 120° F

PTZ

Horizontal Rotation	Not applicable
Vertical Tilt	Not applicable
Preset and Cruise Patterns	Not applicable

AUDIO

Audio Range	Not applicable
Audio Microphone	Not applicable

CONNECTIVITY

Connector Types	BNC
Other Connections	2.1mm power
Wireless	No

POWER

Power Supply	12V 500mA
Power Consumption	<10W (LEDs ON)