




msi[®]

AEGIS

Harness the power of gamers

Waiting for orders, build to comply. Get ready to feel the full power of gaming with this fully equipped battle station. Featuring advanced speed with PCI-E Gen.3 SSD, data transmission speed reaches up to 2100MB/s which is 4x faster than that of most SATA 3 SSDs. While the new Mystic Light feature will give you the power to set your case like it's on fire or as cold as ice. Aegis will harness the power for pure gaming.



Windows 10

Windows 10. Do great things.



Selling Points

- NVIDIA® GeForce® GTX 960 4G GDDR5 graphics
- 6th Gen Intel® Core™ i5-6400 processor with DDR4 memory
- Supports NVMe PCI-E Gen3 SSD speed up to 2.1GB/s
- Super speed USB 3.1 Gen 1 Type C with reversible design
- Audio Boost 3: Reward your ears with studio grade sound quality
- Nahimic 2.0 Audio Enhancer
- Steel Series Certified, enhance your gaming experience
- Mystic Light LED design
- High quality and durable components Military Class 4
- Super Charger 2: super power delivery, fast charge your mobile device
- All new Gaming Center application
- Exclusive MSI Dragone Eye application
- Windows 10 Home 64-bit

Performance



Visuals




Audio



I/O Overview



- Super Multi DVD
- Dragon shield LED
- Power button
- MIC in
- Headset out
- USB 3.1 Gen 1 type C
- 2 x USB 2.0
- (Top with Super Charger 2)




Audio jack / S/PDIF

USB 3.1 Gen 1

RJ 45 / USB 3.1 Gen 1

HDMI / DP

PS2 / USB 2.0

**msi**®

Windows 10

Windows 10. Do great things.

Aegis

Product Name	Aegis	
Part Number	-	
EAN	-	
System OS	Windows 10 Home	
Processor	Type CPU Frequency / Cache Size CPU Cores/ Thread / CPU TDP	Intel® Core™ i5 6400 Processor 2.7 GHz Turbo to 3.3GHz / 6M Cache 4 / 4 / 65 Watt
Chipset	Intel® B150	
VGA	Graphic VRAM	NVIDIA® GeForce® GTX™ 960 4GB GDDR5
Memory	Type Configuration Maximum	DDR4 8GB 2133 MHz DDR4 So-DIMMs slots x 2 Expandable to 32GB
Storage	Type Signal Maximum Optical Drive	1TB 3.5" HDD 7200RPM + 128GB M.2 SATA SSD 4x SATAIII / 1 x M.2 PCI-E 2x 3.5" HDD / 1 x 2.5" HDD/SSD / 1x M.2 PCI-E SSD (SATA-SSD Combo) DVD Super Multi
Audio	Internal Microphone Audio Chipset Speaker	- Realtek ALC1150 -
Audio Jack	Mic-in/ Headphone out Line-in/ Line-out SPDIF	1 / 1 1 / 4 1
Communication	Wireless LAN LAN (RJ45) Bluetooth	802.11 b/g/n/ac (Intel AC3165) 10/100/1000 (Realtek 8111H) 1 x BT 4.2
I/O	USB (front/ side/ rear q'ty) HDMI-in / HDMI-out Display port-in / Display port-out Gaming device port(PS/2)	9 (1x USB 3.1 Gen 1 type C, 2x USB 2.0 type A / non / 4x USB 3.1 Gen 1 type A, 2x USB 2.0 type A) - / 1 - / 1 1
Others I/O	-	
Extension	-	
Mechanical and Environmental	Operating, Storage Temperature Operating, Storage Humidity Regulatory Compliance	10 - 35°C, -20 - 60°C 40 °C 85% and 0 °C 0%, -20°C ~ 60 °C ; 0% ~ 90% Safety: UL/CB, EMC:CE/FCC/C-TICK/VCCI/BSMI
Noise	32 db@ Full Loading; 22 db@ Idle Mode	
Lock	Side panel security lock	
Wake-on-LAN	YES	
KB / Mouse	USB Gaming KB/Mouse (Optional)	
VESA Mount	-	
Power	Power supply	350W 80PLUS bronze certified
Dimension (W x H x D)	433.18mm x 376.11mm x 169.92mm (19.6L)	
Weight	Net / Gross Weight	8KG / 10.5KG
Warranty	2 Years Warranty	
Accessories	Power Cord	K33-3001002-I45 (USA) K33-3001005-I45 (EU) K33-3001081-I45 (UK)