

Heavy-Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 3 ft. (0.91 m), Red

MODEL NUMBER: P005-003-ARD



Computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 3 ft.

Features

C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This computer power extension cord features a red SJT jacket and fully molded red ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Highlights

- Recommended for powering computers, servers and other network devices
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Color-coded red for fast, easy identification in a crowded rack or workstation
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 3 ft. away in your data center
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P005-003-ARD Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 3 ft., Red

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332199003
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	250
PHYSICAL	
Color	Red
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Cable Length (cm)	91.44
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.15 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.90 x 7.00 x 0.50
Shipping Weight (kg)	0.20
Shipping Weight (lbs.)	0.44
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>