

ThinkCentre M600 Tiny Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Celeron® Processor N3000 Series or Intel Pentium® Processor N3000 Series						Keyboard	<p>Some: PS/2 Keyboard (PS/2 connector), Lenovo logo</p> <p>Some: Preferred Pro USB Keyboard (USB connector), Lenovo logo</p> <p>Some: Lenovo USB Fingerprint Keyboard (USB connector)</p> <p>Some: Ultrathin Plus Wireless Keyboard (2.4GHz via USB receiver), black</p> <p>Some: PS/2 Optical Wheel Mouse, black, Lenovo logo</p> <p>Some: Enhanced Optical USB Mouse, black, Lenovo logo</p> <p>Some: Ultrathin Plus Wireless Mouse (2.4GHz via USB receiver), black</p>																	
Processor	Cores / Threads	Frequency (Base/Max)	Cache	Memory Types	Integrated Graphics		Mouse	<p>Some: PS/2 Keyboard (PS/2 connector), Lenovo logo</p> <p>Some: Preferred Pro USB Keyboard (USB connector), Lenovo logo</p> <p>Some: Lenovo USB Fingerprint Keyboard (USB connector)</p> <p>Some: Ultrathin Plus Wireless Keyboard (2.4GHz via USB receiver), black</p> <p>Some: PS/2 Optical Wheel Mouse, black, Lenovo logo</p> <p>Some: Enhanced Optical USB Mouse, black, Lenovo logo</p> <p>Some: Ultrathin Plus Wireless Mouse (2.4GHz via USB receiver), black</p>																	
Celeron N3000	2 / 2	1.04 / 2.08 GHz	2MB	DDR3L-1600	Intel HD																				
Celeron N3050	2 / 2	1.6 / 2.16 GHz	2MB	DDR3L-1600	Intel HD																				
Pentium N3700	4 / 4	1.6 / 2.4 GHz	2MB	DDR3L-1600	Intel HD																				
Chipset	Intel Architecture (IA) SoC that integrates Intel processor core, graphics, memory controller, and I/O interfaces into a single system-on-chip solution						Mechanical	<ul style="list-style-type: none"> • Tiny (1L or 2L), black color; metal case 																	
Graphics	Intel HD Graphics in processor, uses main memory, DirectX® 11.1, twoDisplayPort™, one optional 3rd DP or VGA, supports triple independent display; Maximum resolution: 3840x2160(DP)@30Hz; 1920x1200(optional VGA)@60Hz; 1920x1080(DP to VGA dongle)@60Hz; 1920x1080(DP to DVI dongle)@60Hz; 3840x2160(DP to HDMI dongle)@30Hz							<table border="1"> <thead> <tr> <th></th><th>Dimensions (WxDxH)</th><th>Max weight (lb / kg)</th></tr> </thead> <tbody> <tr> <td>M600 Tiny only (1L)</td><td>7.05" X 7.20" X 1.36" 179mm X 182.9mm X 34.5mm</td><td>2.9 lb (1.3 kg)</td></tr> <tr> <td>M600 Tiny only (2L)</td><td>7.05" X 7.20" X 3.15" 179mm X 182.9mm X 80mm</td><td>4.2 lb (1.9 kg)</td></tr> <tr> <td>M600 Tiny (1L) with VESA mount & ODD box</td><td>7.42" X 7.30" X 2.48" 188.4mm X 185.38mm X 63mm</td><td>4.12 lb (1.87 kg)</td></tr> <tr> <td>M600 Tiny (1L) with VESA mount & I/O box</td><td>7.42" X 7.30" X 2.62" 188.4mm X 185.38mm X 66.6mm</td><td>3.53 lb (1.6 kg)</td></tr> </tbody> </table>				Dimensions (WxDxH)	Max weight (lb / kg)	M600 Tiny only (1L)	7.05" X 7.20" X 1.36" 179mm X 182.9mm X 34.5mm	2.9 lb (1.3 kg)	M600 Tiny only (2L)	7.05" X 7.20" X 3.15" 179mm X 182.9mm X 80mm	4.2 lb (1.9 kg)	M600 Tiny (1L) with VESA mount & ODD box	7.42" X 7.30" X 2.48" 188.4mm X 185.38mm X 63mm	4.12 lb (1.87 kg)	M600 Tiny (1L) with VESA mount & I/O box	7.42" X 7.30" X 2.62" 188.4mm X 185.38mm X 66.6mm	3.53 lb (1.6 kg)
	Dimensions (WxDxH)	Max weight (lb / kg)																							
M600 Tiny only (1L)	7.05" X 7.20" X 1.36" 179mm X 182.9mm X 34.5mm	2.9 lb (1.3 kg)																							
M600 Tiny only (2L)	7.05" X 7.20" X 3.15" 179mm X 182.9mm X 80mm	4.2 lb (1.9 kg)																							
M600 Tiny (1L) with VESA mount & ODD box	7.42" X 7.30" X 2.48" 188.4mm X 185.38mm X 63mm	4.12 lb (1.87 kg)																							
M600 Tiny (1L) with VESA mount & I/O box	7.42" X 7.30" X 2.62" 188.4mm X 185.38mm X 66.6mm	3.53 lb (1.6 kg)																							
Monitor cable	Optional DP to VGA, DP to DVI-D (single link), or DP to HDMI 1.4 dongle																								
Memory	8GB max / DDR3 Low Voltage, DDR3L-1600, non-parity, one 204-pin SO-DIMM socket																								
Storage	<p>Some: M.2 Solid State Drive (SSD), SATA interface</p> <p>Some: hard disk, 5400 or 7200 rpm, SATA 6.0Gb/s, 2.5" Wide</p> <p>Some: 500GB (5400 rpm) Solid State Hybrid Drive (SSHD) / with 8GB MLC NAND flash memory, SATA 6.0Gb/s, 2.5" wide</p>																								
Optical	<p>Some: Solid State Drive (SSD) / SATA 6.0Gb/s, 2.5" Wide</p> <p>Some: external ODD box with DVD-ROM, 9.5mm high, via USB</p> <p>Some: external ODD box with DVD±RW, 9.5mm high, via USB</p> <p>Some: external ODD box (for TIO) with DVD-ROM, 9.5mm high, via USB</p> <p>Some: external ODD box (for TIO) with DVD±RW, 9.5mm high, via USB</p>						VESA mount	Optional VESA mount bracket kit, supports VESA 75mm and 100mm																	
							Floor Stand	Optional system floor stand for vertical orientation																	
Onboard SATA Media reader	SATA 6.0Gb/s controller, one connectors on planar						Power supply	65 watts AC/DC adapter, autosensing, 88% PSU (not included for TIO models) 90 watts AC/DC adapter, autosensing, 88% PSU (only for models with I/O box)																	
	None						Limited warranty ³	<p>Some: 1-year or 3-year, depot service / service upgrades available</p> <p>Some: 1-year or 3-year, limited onsite service / service upgrades available</p> <p>Some: 3-year, limited onsite service, OID (Onsite International Delivery) / service upgrades available</p>																	
								For Lenovo service upgrade options, please go to S-TC sheet																	
Front ports	Two USB 3.0 (one is Always On and fast charge), one microphone (stereo, 3.5mm), one headphone / microphone combo jack (stereo, 3.5mm)						Preload	<p>Some: Windows® 7 Professional 64 preinstalled through downgrade rights in Windows 10 Pro 64-bit</p> <p>Some: Windows 7 Professional 64</p> <p>Some: Windows® 10 Pro 64-bit</p> <p>Some: Windows 10 Home 64-bit</p>																	
Rear ports	Two USB 2.0, two USB 3.0 (optional external optical box or I/O box occupies one or two specific USB on some models), ethernet (RJ-45), two DisplayPort, one optional port (VGA, 3rd DP, or serial on some models), one headphone; additional four serial (9-pin), one parallel (25-pin), and two PS/2 ports on 2L models							<p>Some: Windows® Embedded Standard 7 (WES 7)</p> <p>Some: LeTOS (Lenovo Terminal Operating System, Linux-based)</p>																	
I/O box	Optional external I/O box, extends two USB 2.0, two USB 3.0, and one serial on rear, two USB 2.0 on front, via USB (occupy two specific USB 3.0 of M600 Tiny)							Preloaded applications (only some listed)																	
Audio support	High Definition (HD) Audio, Realtek ALC223 / optional internal speaker (1 watt)							<p>- WES 7 only:</p> <ul style="list-style-type: none"> • Desktop Power Manager • Lenovo Solution Center • Lenovo REACHit • Lenovo SHAREit • Lenovo Bluetooth Lock • McAfee® LiveSafe™ (30-day trial) • Microsoft Office preloaded; purchase a product key to activate • PowerDVD Create (DVD±RW) • Lenovo ThinkVantage Tools 																	
WLAN ¹³	<p>Some: 11ac wireless, M.2 Card, Realtek RTL8821AE (dual band), Wi-Fi + Bluetooth 4.0 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Qualcomm Atheros QCA9377 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Qualcomm Atheros QCA6174 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 2x2</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 3165, Wi-Fi + Bluetooth 4.0 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 8260, Wi-Fi + Bluetooth 4.1 combo adapter, 2x2</p>							<p>- Only for Window 10</p> <ul style="list-style-type: none"> • Lenovo Companion (Win10) • Cyberlink PowerDVD (DVD, DVD±RW) • Lenovo QuickOptimizer 																	
Bluetooth™	Some: Bluetooth 4.0 or 4.1 wireless, integrated in Wi-Fi + BT combo adapter							<p>- Only for Window 7</p> <ul style="list-style-type: none"> • Rescue and Recovery • Password Manager • ThinkVantage System Update • Lenovo Message Center Plus • Adobe® Reader® 																	
Ethernet Modem	One gigabit ethernet port, Realtek RTL8111GN, Wake on LAN®							<p>- LeTOS only:</p> <ul style="list-style-type: none"> • xFreeRDP • Citrix ICA Client • VMware View Client • Java • Mozilla Firefox 																	
Manageability Security chip	None																								
Security features	<ul style="list-style-type: none"> • Security slot (in rear for optional Kensington® MicroSaver® cable) • Padlock loop • Smart USB protection, allows keyboard/ mouse only, blocks all storage devices • Power-on password 																								
	<ul style="list-style-type: none"> • Administrator password • Hard disk password • Boot sequence control • Boot without keyboard and mouse • Individual USB port disablement • Chassis intrusion switch 						Environment	ENERGY STAR® 6.0*, EPEAT™ Gold rating* (*for Windows models only); GREENGUARD®; RoHS-compliant; Cisco EnergyWise compatible; ErP Lot 3																	
							Accessories	For compatible accessories, please go to TC-AQP sheet																	

See footnotes for more detailed information

© Lenovo

(G-EFL1-Spec) January 2016

Model		10G90012US
Product		M600 Tiny
Region		US
Machine Type		10G9
TopSeller		TopSeller
Case 1L/2L		1L
Processor		Pentium N3700
Memory		4GBx1
Graphics		Intel HD
Storage		500GB 7200
External Optical / I/O box		None
WLAN		Intel 3165 ac
Optional Port		None
Monitor Cable		None
Chassis Intrusion Switch		Switch
Floor Stand		Stand
VESA Mount		None
Keyboard/Mouse		USB
Internal Speaker		Speaker
Power Supply		65W
Kensington Cable Lock		None
Preload		Win10 Pro64
Base Warranty (year)		1-onsite
Global		No
Ann Date (mm/yy)		05/16



