



The ViewSonic EP5520T is a 10-point interactive 55" all-in-one free-standing digital ePoster kiosk with a sleek, slim design. Great for grabbing attention in busy, high-traffic areas, the EP5520T comes with a scratch-proof tempered glass faceplate for added durability. Featuring Full HD 1080p resolution, 178°/178° wide-angle viewing, 350-nit brightness, 4,000:1 contrast ratio, and dual 10W stereo speakers, the EP5520T delivers customized multimedia messaging with vivid clarity. Photo and video files can be played back using the embedded Quad-core media player and 16GB of internal memory, or add your own media player using the convenient media player cradle inside the lockable security door.

Interactive On-Demand Messaging

This display delivers on-demand interactive messaging with 10-point multi-touch capability and is the perfect e-catalog display solution for use as retail, information, and wayfinding kiosks in high-traffic areas.

All-in-one with Integrated Media Player

This display features an integrated media player with quad-core processor and 16GB storage, providing smooth and reliable multimedia contents playback – without the need for an external media player or PC.



USB multimedia playback

Customized photos, music, and 1080p video can be quickly displayed on-screen directly from a USB drive.



Access to Web Contents

Integrated with RJ45 connectivity, the display offers convenient web browsing functionality. Users can search online and watch videos directly on the display without having to connect to other computing devices.


Internal scheduler

An efficient, user-friendly scheduling interface is available via the on-screen display (OSD). Setup features include time and date scheduling, ensuring that messaging, images, or videos run smoothly and on time.



Versatile Connectivity

HDMI, USB, and VGA connections provide the versatility to connect to a wide variety of computing and multimedia devices.



Easy Multi-device Management

RS232 connectivity enables computers and laptops to be connected to this display, and also allows IT personnel to conveniently manage multiple displays, and configure devices.

Media player Cradle with Security Door

A convenient media player cradle can accommodate a PC or an additional mounted media player, while a lockable door keeps things secure and out of sight. The ePoster stand also features an integrated power supply, eliminating the need to find alternative outlets for add-on devices.

Dual Integrated Speakers

Designed with dual integrated speakers, this display combines incredible screen performance with stereo sound for an immersive multimedia experience.



Technical Specifications

Display	Panel Size	55" (54.6" Diagonal)
	Type/Tech	TFT LCD Module with WLED
	Display Area (mm)	1209.6 (H) x 680.4 (V)
	Aspect Ratio	9:16
	Native Resolution	1920 x 1080
	Colors	16.7M
	Brightness	350 nits (typ.)
	Contrast Ratio	4000:1 (typ.)
	Response Time	8 ms (typ. G to G)
	Viewing Angles	178°(H), 178°(V)
	Backlight Life	30,000 Hours Typ.
	Surface Treatment	Hard coating (7H)
Touch	Type/ Tech	IR
	Touch Resolution	32768 x 32768
	Touch Point	10 points
Storage	on-board flash	16GB
INPUT	HDMI	x2
	RGB / VGA	x1
	RS232	x1
	Audio	x1 PC audio(3.5 mm)
OUTPUT	Audio	x1 (Earphone out)
LAN	RJ45	x1
USB	Type A	x3 (2.0 x 1, 3.0 x 2)
	Type B	x1 (for touch module)
SPEAKERS		10W x 2
COMPATIBILITY	RGB PC/HDMI PC	1920x1080 @60Hz
	HDMI	1920x1080 @60Hz
Power	Voltage	100-240VAC +/- 10% Wide Range
	Consumption	115W (Typ.)
OPERATING CONDITIONS	Temperature (° C)	0°C to 40°C
	Humidity	20% ~ 80% non-condensing
DIMENSIONS (W x H x D)	Physical (inch / mm)	32.28x74.8x17.72 / 820x1900x450
WEIGHT	Net (lb / kg)	68kgs / 149.91 lbs
REGULATIONS		FCC/cTUVus /TUV-Mexico CoC/Mexico Energy/CE EMC/CB/ErP/PSB/RCM/BSMI
PACKAGE CONTENTS		Power Core / Remote control with battery / Quick Start Guide / User Guide CD / Key