

HDMI/DVI/USB KVM Cable Kit, 10 ft. (3.05 m) - USB 2.0, 4K 60Hz

MODEL NUMBER: P782-010-DH



Connects your HDMI- or DVI-enabled computer to a Tripp Lite HDMI KVM switch up to 10 ft. away.

Description

The P782-010-DH HDMI/DVI/USB KVM Cable Kit connects your computer to a Tripp Lite HDMI-enabled KVM switch. It includes a 10-ft. (3.05 m) USB A/B keyboard/mouse cable, a 10-ft. (3.05 m) HDMI monitor cable and an adapter for converting a DVI port to HDMI. Premium foil and braid shielding in the cables delivers reliable, error-free signal quality and protection from EMI/RFI interference. Integral strain relief ensures the cable and connectors last a long time. The adapter's molded gold-plated connectors and contacts ensure excellent conductivity.

Features

Connects Your Computer to a Tripp Lite HDMI KVM Switch Includes 10 ft. USB A/B cable, 10-ft. (3.05 m) HDMI cable and DVI-to-HDMI adapter. HDMI cable support crystal-clear video resolutions up to 4K x 2K (3840 x 2160) @60Hz. USB A/B cable support data transfer speeds up to 480 Mbps. HDMI to DVI-D adapter support resolutions up to 1920 x 1080 @60Hz.

First-Rate Construction for Superior Signal Transfer Premium foil and braid shielding for EMI/RFI noise protection. Molded gold-plated connectors and contacts for optimal signal quality. Integral strain relief for long life. Flexible PVC jackets easy to install in tight spaces.

Specifications

OVERVIEW	
UPC Code	037332199898
Product Type	Cable Kit
Accessories Type	Cable Kit
Technology	DVI; HDMI

Highlights

- Includes 10-ft. (3.05 m) USB A/B and HDMI cables
- Includes DVI-to-HDMI adapter
- Premium foil and braid shielding
- Integral strain relief
- Molded gold-plated connectors and contacts

System Requirements

- Computer with available USB port and available HDMI or DVI port
- Tripp Lite HDMI KVM switch

Package Includes

- USB 2.0 cable (A/B M/M), 10-ft. (3.05 m)
- HDMI cable (M/M), 10-ft. (3.05 m)
- HDMI to DVI-D Dual Link adapter (F/M)



VIDEO	
Max Supported Video Resolution	HDMI: 3840 x 2160 @60Hz, DVI: 1920 x 1080 @60Hz
PHYSICAL	
Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / cm)	1.27 x 21.08 x 16.26
Shipping Dimensions (hwd / in.)	0.50 x 8.30 x 6.40
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK); HDMI (MALE); USB B (MALE)
Side B - Connector 1	HDMI (MALE); USB A (MALE)
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
USB Specification	USB 2.0 (up to 480 Mbps)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>