



Specification

Update Date:

1/Jul/15

Version: 1

Model Number: SE32HG		32 inch LED QFHD TV		Features		
UPC Code		819456012334		31.5 inch DLED TV		
Display Features				Built in 3D PAL/NTSC Comb Filter		
Diagonal Panel Size		31.5" inch		Built in 3D Video Noise Reduction		
Active Area		701.74(H)mm X 395.34(V)mm		Built in BTSC/SAP		
Aspect Ratio		16:9		Over-The-Air ATSC/NTSC RF Input Support		
Panel Resolution		1366 x R.G.B. x 768 (Pixel)		Digital/Analog Channel auto tuning		
Panel Refresh Rate		50/60Hz		Support V-CHIP/CCD/Favorite Channel Edition		
Brightness		180 cd/m2		HD compatible :480I,576I,480P,576P,720P,1080I ,1080P		
DynamicContrast ratio		1000:1		USB Supports File Format: JPEG/MP3		
Viewing Angle		178°(H) x 178°(V)(CR≥10)		OSD Language: English/French/Spanish		
Dot Pitch		0.51(HmmX0.51(V)mm		Accessories Included		
Maximum Color		16.7M Colours		Remote control*1		
Response time Gray-Gray		6.5 ms		Owners Manual*1		
Electronics				Battery*2		
Scaler Solution		Mstar MSD3393		Power Requirements		
DNR		3D		Power Source		AC100-240V 50/60Hz
Digital Comb Filter / Type		3D		Power ON consumption		≤60W
TV System & Video Standards Supported				Standby consumption		<0.5W
TV System		ATSC/NTSC M		Operating Temperature		5℃-35℃
Channel CATV - UHF/VHF (ATV)		AIR: 2~69;Cable: 1~135		Operating Humidity		20%-80%
Composite / S-Video input		PAL/NTSC		Dimension (WxHxD)		
Video Connections				VESA Dimension (WxH)mm		200x200
Analog&Digital TV Tuner		×1		Unit w/ Stand (in)		28.738"x7.913"x18.226"
Composite Video Input		×1(Y terminal will be the same)		Unit w/o Stand (in)		28.738"x3.555"x16.980"
S-Video Input (4pin DIN)		NO		Carton (in)		31.496"x6.142"x20.709"
Component Input (Y,Cb,Cr/Y,Pb,Pr)		×1		Weight (lbs)		
VGA Input (15 pin D-Sub)		×1		Net Weight w/Stand		8.378 Lbs
DVI-D / DVI-I Input		NO		Net Weight w/o Stand		8.245 Lbs
HDMI Input		×3		Gross Weight		11.729 Lbs
USB		×1		Warranty & Support		
Audio				One Year Manufacture Warranty		
Maximum Audio Output		2×8W		Toll Free Customer Support		
Number of speakers		×2		On-Line Manual / Firmware Access		
Audio Surround		Yes		Logistic		
Audio Connections				Standard Pallet Unit Load		NO
Stereo Mini Phono Jack Input (3.5mm)		NO		20' GP Container Unit Load w/o Pallet		400
RCA Input		×1(R/L)		40' GP Container Unit Load w/o Pallet		810
Headphone: Stereo Mini (3.5mm)		×1		40' HQ Container Unit Load w/o Pallet		1010
LINE OUT(MINI)		NO				
Optical Digital Output		×1				
VGA Resolutions Supported						
640x480						
800x600						
1024x768						
1366 x 768						
This spec may change from time to time,we are not liable for any misrepresentation if we post the wrong specs on the sheet						