

DISPLAY

AVAILABLE COLORS



Black



KEY FEATURES

- Outdoor-safe, built for permanent outdoor installation (full shade applications). Indoor TV manufacturers specifically prohibit outdoor use (just check the manual). Don't risk safety and your warranty by using an indoor TV outdoors.
- Premium 4K UHD screen with direct LED backlight delivers breathtaking, dramatic picture detail with 4 times the resolution of Full HD
- Up to 30% brighter than indoor TVs for improved viewing in brighter outdoor environments
- Supports HDMI 2.0 and HDCP 2.2 ensuring compatibility with the latest 4K sources and streaming services.
- Powder-coated rust-proof aluminum exterior protects internal components from rain, snow, dust, insects, humidity, and salt air
- Innovative weather-tight cable entry system seals out moisture and allows for easy hook-ups
- Large media bay with plenty of room for many popular media players, cables, baluns, and extenders.
- Built-in 20W down-firing speakers for an all-in-one sound solution, or add an external audio system
- Dispersive temperature regulation system allows operation in low temperatures from -24°F and high temperatures up to 104°F (Storage temperature from -24°F up to 140°F).
- Rear IR receiver in media bay keeps IR emitter hidden & protected
- Weatherproof remote control. Leave it outdoors. Conveniently ready when you need it.
- 4 HDMI and 2 USB inputs provide plenty of connectivity options
- Optional outdoor dust cover (not included)

SCREEN	<div> <div>SCREEN</div> <div>55-inch Diagonal Color Active Matrix TFT LED</div> </div> <div> <div>RESOLUTION</div> <div>3840 x 2160 UHD</div> </div> <div> <div>ASPECT RATIO</div> <div>16:9</div> </div> <div> <div>CONTRAST RATIO</div> <div>4000:1</div> </div> <div> <div>FRAME RATE</div> <div>60 Hz</div> </div> <div> <div>VIEWING ANGLE</div> <div>178° x 178°</div> </div> <div> <div>RESPONSE TIME</div> <div>6.5 milliseconds</div> </div> <div> <div>TV FORMATS</div> <div>2160p, 1080p, 1080i, 720p, 720i, 480p, 480i</div> </div>
CONNECTIONS	<div> <div>RF</div> <div>Antenna/CATV (ATSC/QAM/NTSC) x1</div> </div> <div> <div>HDMI</div> <div>HDMI™ Input x4 (HDMI 1.4, HDMI 2.0, HDCP 2.2) 3840 x 2160 @ 60hz</div> </div> <div> <div>VIDEO COMPOSITE</div> <div>Composite Video x1, L/R Audio Inputs x1</div> </div> <div> <div>VIDEO COMPONENT</div> <div>YPbPr plus Stereo Audio x1</div> </div> <div> <div>CONTROL SET</div> <div>Concealed Rear IR Window</div> </div> <div> <div>AUDIO OUT</div> <div>Digital TosLink Optical Audio(fixed) RCA L+R (variable)</div> </div> <div> <div>SPEAKERS</div> <div>20 WATT internal speakers</div> </div> <div> <div>INPUT POWER</div> <div>100-240 VAC, 50-60 Hz 2.8 A Max (125 Watts/1.0a@120v)</div> </div>
TEMPERATURE TOLERANCES	<div> <div>OPERATING TEMP</div> <div>-24° to 104° F. (-31° to 40°C.)</div> </div> <div> <div>NON-OP. TEMP</div> <div>-24° to 140° F. (-31° to 60°C.)</div> </div>
PHYSICAL SPECS	<div> <div>ACCESSORIES INCLUDED</div> <div>Weatherproof remote control</div> </div> <div> <div>EXTERIOR</div> <div>Powder-coated aluminum</div> </div> <div> <div>EXTERIOR COLORS</div> <div>Black only</div> </div> <div> <div>TV DIMENSIONS</div> <div>50" W x 29 " H x 3.86" D (1260mm W x 740mm H x 98mm D)</div> </div> <div> <div>TV WEIGHT</div> <div>51 lbs (23.1 kgs)</div> </div> <div> <div>VESA MOUNT PATTERN</div> <div>400mm x 400mm</div> </div> <div> <div>SHIPPING DIMENSIONS</div> <div>56.5" W x 37 " H x 9" D</div> </div> <div> <div>SHIPPING WEIGHT</div> <div>63 lbs</div> </div> <div> <div>RESIDENTIAL WARRANTY</div> <div>1 Year Parts and Labor</div> </div>

Specifications

SunBriteTV Model SB-5574HD

LCD Screen	55-inch diagonal Color Active Matrix TFT LED LCD
Resolution	3840 x 2160 UHD 4k
Aspect Ratio	16:9
Contrast Ratio	4000:1
Frame Rate	60hz
H/V Viewing Angle	178° by 178°
Response Time	6.5 milliseconds
TV formats	2160p*,1080p, 1080i, 720p, 720i, 480p, 480i * using HDMI only
Input Connectors:	
RF	Antenna/CATV (NTSC/ATSC/QAM) x1
HDMI	HDMI Input x4 (Supports HDMI 1.4, HDMI 2.0, HDCP 1.4 & HDCP 2.2)
Video Composite	Composite Video x1, L/R Audio Inputs x1
Video Component	YPbPr plus Stereo Audio x1
Control Set	Discrete IR Control, Concealed rear IR receiver
Audio Out	Tos-Link Optical audio (Fixed) Analog RCA jacks (variable)
Speakers	20 Watt downfiring internal speakers
Exterior	Powder-coated aluminum
Colors	Black only
Input Power	100-240 VAC, 50-60 Hz 2.8A Max (125 watts/1.0a@120v)
Operating Temp.	32° to 104° F. (0° to 40° C.)
Non-op. Temp.	-24° to 140° F. (-31° to 60° C.)
Accessories Included	Weatherproof remote control with battery.
TV Dimensions	49.6" W x 29" H x 3.86" D 1480mm W x 863mm H x 102mm D
TV Weight	51 lbs.(23.1 kgs)
Residential Warranty	1 year
Commercial Warranty	1 year
Vesa Mount Pattern	400mm x 400mm

