


4MP Bullet IP Camera with Junction Box

O4B7 2.8mm fixed lens, dark grey housing

Features

- Supports up to 4MP @ 30fps in 16:9 widescreen format
- Built-in standard PoE (IEEE 802.3af)
- Adaptive IR LEDs reduce IR saturation
- IR Range: 98' (depending on scene reflection)
- True Day/Night operation (IR cut filter)
- True WDR (wide dynamic range) operation
- IP67 compliant, weather resistant
- Junction box included
- Conformant with ONVIF Profile S
- 5 year warranty



Included Junction Box (O2VLJBB)

Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 4MP
Maximum Resolution	2688 x 1520
Minimum Illumination	F2.0, 0.08 lux color; 0 lux (IR LED on)
IR Range	98' (depending on scene reflection)
White Balance	Auto / Presets / Manual
Compensation	WDR (120dB)/BLC/HLC
Day/Night	IR cut filter
Exposure Control	Digital slow shutter
Electronic Shutter Speed	1/3 - 1/100000 sec
DNR	3D

Video Specifications

Supported Resolutions	2688x1520 / 2560 x 1440 / 1920x1080 / 1280x720 @ 30fps
Compression	H.264, MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams

Audio Specifications

Mono Input	N/A
Mono Output	N/A

External Terminal Specifications

Ethernet	10/100 Mbps
Power	DC jack

Network Specifications

Protocols	IPv4, IPv6, TCP, UDP, RTCP, RTP, RTSP, HTTP, HTTPS, SMTP, SNMP, UPnP, FTP, DHCP, Bonjour, QoS, 802.1x
DDNS support	Speco DDNS (free of charge)

Network Specifications (continued)

Security	User ID & Password protection, IP address filtering
User Access	20 simultaneous users (performance may vary depending on resolution and number of connections)

System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection, face detection
Alarm Triggers	Analytics, network loss, sensor input
Alarm Events	FTP video/image file upload, email image upload
Video Buffer	Configurable pre-record & post-record
Image Settings	Privacy mask

Client Specifications

Web Browser Support	Windows (Internet Explorer 11)
PC Application	SecureGuard®
Mobile	SecureGuard® Mobile (iPhone® and Android™)

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	6.5W max
Operating Temperature	-22°F -140°F
Operating Humidity	0% - 95% RH
Unit Dimensions	2.8" (Dia.) x 6.5" (L)
Unit Weight	1 lb.
Certifications	FCC, RoHS, UL

Optional Accessories



POEINJ
12.95W
PoE Injector



PSW5
12VDC
Power Supply