

# PP Filament 1.75mm 500g Reel – Natural (55950)

**Reorder Number** 55950

**Pack Size** 1 ea

Manufactured to very tight tolerances and from the highest quality materials, Verbatim PP 3D Printing Filament offers high levels of heat and chemical resistance, compared to other 3D filaments. PP filament is commonly used for food packaging, medical applications, IT equipment, and other applications that require softness and heat resistance. Verbatim Filament is designed for compatibility with most commercially available FFF 3D printers. With diameter tolerances of  $\pm 0.05$ mm, Verbatim PP 3D Filaments ensure consistent feeding and stable prints, every time. Verbatim 3D Filaments feature a custom spool designed for strength and balance for uniform feeding. Filaments are packaged in a vacuum-sealed bag, including desiccant, to promote longevity and prevent the introduction of moisture. Verbatim PP 3D Printing Filaments are backed by a 1-year limited warranty.



- PP (Polypropylene) filament for use with 3D printers – high heat resistance yet soft
- Manufactured to very tight tolerances (+0.05mm diameter) using the highest quality materials to ensure consistent feeding and stable prints
- Custom spool designed for strength, uniform performance and trouble-free feeding
- Filaments packaged in vacuum-sealed bag, with desiccant to prevent introduction of dust and moisture.
- Compatible with most commercially available non-cartridge based 3D printers.
- For best performance, an extrusion temperature of 220°C is recommended.
- Heated build platform temperature: 100°C recommended.
- Double-sided adhesive tape recommended for bed.
- 1-Year Limited Warranty

## Specifications

**Diameter Tolerance** ..... 1.75 + 0.05 mm

**Process Temperature** ..... 220°C (recommended)

**Net Weight (lbs)** ..... 1.10 lbs (0.50 kg)

**Gross Weight (lbs)** ..... 3.00 lbs (1.36 kg)

**Spool diameter (In)** ..... 7.87 in (20.00 cm)

**Spool depth (In)** ..... 2.83 in (7.20 cm)

**Hub diameter (In)** ..... 4.02 in (10.20 cm)

**Hub hole diameter (In)** ..... 2.01 in (5.10 cm)

Product Information			
<b>L x D x H (In)</b>	7.87 x 7.87 x 2.83 (19.99 x 19.99 x 7.19 in cm)	<b>Weight (lbs)</b>	3.00 lbs (1.36 kg)
Packaging Information			
<b>L x D x H (In)</b>	8.16 x 3.19 x 8.16 (20.73 x 8.1 x 20.73 in cm)	<b>Weight (lbs)</b>	3.31 lbs (1.5 kg)
<b>UPC#</b>	02394255950 4	<b>Unit Quantity</b>	1 ea
<b>Pallet Quantity</b>	180 (1 ea)	<b>Cartons Per Layer</b>	20
<b>Layers Per Pallet</b>	3		
Master Case Information			
<b>L x D x H (In)</b>	8.81 x 8.81 x 10.81 (22.38 x 22.38 x 27.46 in cm)	<b>Weight (lbs)</b>	10.71 lbs (4.86 kg)
<b>UPC#</b>	5002394255950 9	<b>Quantity</b>	3 (1 ea)
Shipping Information			
<b>Available Ship Date</b>	In Stock	<b>Country of Origin</b>	JP
<b>Tariff Code</b>	3916.90.1000	<b>Warranty</b>	1-Year Limited Warranty
<b>Minimum Order Qty</b>	3 (1 ea)		

#### Keywords

55950,#55950,PP Filament 1.75mm 500g Reel – Natural,PP Filament, 1.75mm PP Filament, 3D Filament, 1.75mm 3D Filament, 3D Printing, 3D Printing Supplies, 3D Printing Filament, 3D Printing Filaments