

2MP H.265 License Plate Capture Bullet IP Camera

O2LPR67 5-50mm motorized auto iris varifocal lens (10x auto focus/zoom), white housing

Note: Because of the special nature of this camera, during the day the scene will be monochrome. All license plates will be highlighted. Can be changed to color if desired in the OSD.

Features

- High-contrast imaging performance that delivers sharp, clear license-plate captures
- Up to full HD 1080p @ 30fps
- 15 super high powered IR LEDs
- Captures license plates up to 60mph
- IR Range: 165 ft. (depending on scene reflection)
- True Wide Dynamic Range operation (WDR)
- Triple-codec operation – H.265/H.264/MJPEG
- IP66 compliant, weather resistant
- 2 year warranty

Specifications

Image Sensor	1/3" CMOS Sensor, 2MP
Maximum Resolution	1920x1080 (Full HD)
Minimum Illumination	0 lux (IR LEDs on)
Type	Monochrome
IR LEDs	15
IR Range	165' (depending on scene reflection)
TV System	NTSC
S/N Ratio	More than 50db

Video Specifications

Main Resolution	1920x1080 (1080p), 1280x720 (720p) 704x480 (D1), 640x360, 352x240
Compression	H.265, H.264(MP), MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams


External Terminal Specifications

Ethernet	10/100 Mbps
Power	DC jack
Audio	1 mic in
Video Output	1 BNC
Audio Input / Output	1 line in / 1 line out
Alarm Input	1TTL, NC/NO programmable, 4.3V (NC) or 0.3V (NO) Threshold, 5 VDC
Alarm Output	1 relay out, NO only, 0.3A @ 125 VAC, 1A @ 30 VDC

Network Specifications

Protocols	IPv4, TCP, UDP, RTSP, HTTP, SMTP, FTP, DHCP
Security	User ID & Password protection, IP address filtering
User Access	4 users max.

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 10/27/16



System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection, tampering
Alarm Triggers	Analytics
Alarm Events	Email, alarm, FTP
Image Settings	Privacy mask

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up)
PC Application	SecureGuard® VMS
Mobile	SecureGuard® Mobile (iPhone® and Android™)

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	IR LED On: 1.1A max.
Unit Dimensions	13.58" (L) x 7.23" (H) x 5.12" (Dia.)
Unit Weight	4.41 lbs.
Included in Package	Unit, CD (manual, software), mounting screws



Optional Accessories



INTJBSW
Square
Junction Box



INTCMW
Corner/Pole
Adapter



PSW5
12VDC
Power Supply